

HRC cartridge fuses



LF300G

gG type

Description	Pack qty.	Art No.
Cylindrical fuse-links 10x38mm gG 0.5A	10	LF300G
Cylindrical fuse-links 10x38mm gG 1A	10	LF301G
Cylindrical fuse-links 10x38mm gG 2A	10	LF302G
Cylindrical fuse-links 10x38mm gG 4A	10	LF304G
Cylindrical fuse-links 10x38mm gG 6A	10	LF306G
Cylindrical fuse-links 10x38mm gG 8A	10	LF308G
Cylindrical fuse-links 10x38mm gG 10A	10	LF310G
Cylindrical fuse-links 10x38mm gG 12A	10	LF312G
Cylindrical fuse-links 10x38mm gG 16A	10	LF316G
Cylindrical fuse-links 10x38mm gG20A	10	LF320G
Cylindrical fuse-links 10x38mm gG25A	10	LF325G
Cylindrical fuse-links 10x38mm gG 32A	10	LF332G
Industrial fuse-links 14x51 gG 2A	10	LF402G
Industrial fuse-links 14x51 gG 4A	10	LF404G
Industrial fuse-links 14x51 gG 6A	10	LF406G
Industrial fuse-links 14x51 gG 8A	10	LF408G
Industrial fuse-links 14x51 gG 10A	10	LF410G
Industrial fuse-links 14x51 gG 12A	10	LF412G
Industrial fuse-links 14x51 gG 16A	10	LF416G
Industrial fuse-links 14x51 gG 20A	10	LF420G
Industrial fuse-links 14x51 gG 25A	10	LF425G
Industrial fuse-links 14x51 gG 32A	10	LF432G
Industrial fuse-links 14x51 gG 40A	10	LF440G
Industrial fuse-links 14x51 gG 45A	10	LF445G
Industrial fuse-links 14x51 gG 50A	10	LF450G
Cylindrical fuse-links 22x58mm gG 16A	10	LF516G
Cylindrical fuse-links 22x58mm gG 20A	10	LF520G
Cylindrical fuse-links 22x58mm gG 25A	10	LF525G
Cylindrical fuse-links 22x58mm gG 32A	10	LF532G
Cylindrical fuse-links 22x58mm gG 40A	10	LF540G
Cylindrical fuse-links 22x58mm gG 50A	10	LF550G
Cylindrical fuse-links 22x58mm gG 63A	10	LF563G
Cylindrical fuse-links 22x58mm gG 80A	10	LF580G
Cylindrical fuse-links 22x58mm gG 100A	10	LF590G
Cylindrical fuse-links 22x58mm gG 125A	10	LF599G

aM type

Description	Pack qty.	Art No.
Cylindrical fuse-links 10x38mm aM 0,5A	10	LF300M
Cylindrical fuse-links 10x38mm aM 1A	10	LF301M
Cylindrical fuse-links 10x38mm aM 2A	10	LF302M
Cylindrical fuse-links 10x38mm aM 4A	10	LF304M
Cylindrical fuse-links 10x38mm aM 6A	10	LF306M
Cylindrical fuse-links 10x38mm aM 8A	10	LF308M
Cylindrical fuse-links 10x38mm aM 10A	10	LF310M
Cylindrical fuse-links 10x38mm aM 12A	10	LF312M
Cylindrical fuse-links 10x38mm aM 16A	10	LF316M
Cylindrical fuse-links 10x38mm aM 20A	10	LF320M
Cylindrical fuse-links 10x38mm aM 25A	10	LF325M
Cylindrical fuse-links 10x38mm aM 32A	10	LF332M
Industrial fuse-links 14x51 aM 2A	10	LF402M
Industrial fuse-links 14x51 aM 4A	10	LF404M
Industrial fuse-links 14x51 aM 6A	10	LF406M
Industrial fuse-links 14x51 aM 8A	10	LF408M
Industrial fuse-links 14x51 aM 10A	10	LF410M
Industrial fuse-links 14x51 aM 12A	10	LF412M
Industrial fuse-links 14x51 aM 16A	10	LF416M
Industrial fuse-links 14x51 aM 20A	10	LF420M
Industrial fuse-links 14x51 aM 25A	10	LF425M
Industrial fuse-links 14x51 aM 32A	10	LF432M
Industrial fuse-links 14x51 aM 40A	10	LF440M
Industrial fuse-links 14x51 aM 45A	10	LF445M
Industrial fuse-links 14x51 aM 50A	10	LF450M
Cylindrical fuse-links 22x58mm aM 16A	10	LF516M
Cylindrical fuse-links 22x58mm aM 20A	10	LF520M
Cylindrical fuse-links 22x58mm aM 25A	10	LF525M
Cylindrical fuse-links 22x58mm aM 32A	10	LF532M
Cylindrical fuse-links 22x58mm aM 40A	10	LF540M
Cylindrical fuse-links 22x58mm aM 50A	10	LF550M
Cylindrical fuse-links 22x58mm aM 63A	10	LF563M
Cylindrical fuse-links 22x58mm aM 80A	10	LF580M
Cylindrical fuse-links 22x58mm aM 100A	10	LF590M
Cylindrical fuse-links 22x58mm aM 125A	10	LF599M



LF300M