



FWB42GS

FWB encl., univers, IP44,650x550x161, QC

Product Datasheet

Architecture

Fixing mode	flush-mounting/surface-mounting/section make
-------------	--

Configuration

Module	with terminals
--------	----------------

Compatibility

Compatible with DIN rail mounting	yes
-----------------------------------	-----

Electric current

Rated current	125 A
---------------	-------

Cover, door

Type of door closing	hinged pattern handle
Number of keylock of the door	1
Cover type	With Notch
Door leave	single
Door quantity	1
Cover type	Door
Transparent cover or door	yes

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	Steel

Dimensions

Depth of installed product	165 mm
Internal depth	156 mm
Height of installed product	650 mm
Installation height	650 mm
Width of installed product	550 mm
Width in division units	12

Installation, mounting

Suitable for outdoor use	no
--------------------------	----

Accessories included

Mounting plate included	no
With lock	no

Equipment

Number of rows	8
Quantity of section in width	2
Number of keys	1
Quantity of rails	8
Can be accessorized	yes
Extension possible	yes

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP44
Protection class	isol.class II