



MZ201

**Auxiliary contact 1C+1O 6A 240V AC**

Product Datasheet

**Main electrical features**

Type of supply voltage	AC
Rated operational voltage $U_e$	230/415 V

**Voltage**

Rated insulation voltage	4000 V
Max operating voltage	240 V
Rated operational voltage in DC	12/250 V

**Electric current**

Acceptable current rating with AC1	6 A
$I_{min}=f(U=12V DC)$ for power circuit	0,3 A
$I_{min} = f (U = 230 V DC)$	0,6 A
$I_{min}=f(U=400V AC)$ for power circuit	3 A

**Power**

Total power loss under IN	0,1 W
---------------------------	-------

**Endurance**

Electric endurance in number of cycles	6000
Number of mechanical operations	12000

**Dimensions**

Depth of installed product	40 mm
Height of installed product	80 mm
Width of installed product	9,5 mm

**Installation, mounting**

Tightening torque	1,2Nm
Factory fitted	no

**Connection**

Connection cross-sect. rigid cable	10mm <sup>2</sup>
Connection cross-sect. flexible conductor	6mm <sup>2</sup>
Type of connection	with screw
Type of contacts	1NC+1NO

**Equipment**

Quantity of NC contacts	1
Quantity of NO contacts	1

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Use conditions**

---

Storage temperature	-40 to 80 °C
Air humidity protection	95% / 80°C

---