



MZ202

Alarm contact 1C+1O 6A 240V AC

Product Datasheet

Main electrical features

Rated operational voltage U _e	230/415 V
--	-----------

Voltage

Rated insulation voltage	4000 V
Max operating voltage	240 V
Rated operational voltage in DC	12/250 V

Electric current

Acceptable current rating with AC1	6 A
I _{min} =f(U=12V DC) for power circuit	0,3 A
I _{min} = f (U = 230 V DC)	0,6 A
I _{min} =f(U=400V AC) for power circuit	3 A

Power

Total power loss under I _N	0,2 W
---------------------------------------	-------

Endurance

Electric endurance in number of cycles	6000
Number of mechanical operations	12000

Dimensions

Depth of installed product	68 mm
Width of installed product	9 mm

Installation, mounting

Tightening torque	1,3Nm
Factory fitted	no

Connection

Connection cross-sect. rigid cable	10mm ²
Connection cross-sect. flexible conductor	6mm ²
Type of connection	with screw
Type of contacts	1NC+1NO

Equipment

Quantity of NC contacts	1
Quantity of NO contacts	1

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Storage temperature	-40 to 80 °C
Air humidity protection	95% / 80°C
