



MZ206

## Under voltage release 230V AC

Product Datasheet

### Functions

Switch-off delay	no
Switch-on delay	no

### Main electrical features

Rated operational voltage U <sub>e</sub>	230 V
Type of supply voltage	AC
Frequency	50/60 Hz

### Voltage

Rated insulation voltage	4000 V
Command voltage AC	230 V

### Electric current

Acceptable current rating with AC1	15 mA
------------------------------------	-------

### Power

Inrush power absorbed	3,5 VA
Total power loss under I <sub>N</sub>	2 W

### Tripping

Time of response when opening	200 ms
Performance voltage / Tripping at U <sub>e</sub>	35 / 70 %

### Dimensions

Depth of installed product	68 mm
Width of installed product	17,5 mm

### Installation, mounting

Tightening torque	1,2Nm
360° product mounting position	yes

### Connection

Connection cross-sect. flexible conductor	6mm <sup>2</sup>
Connection cross-sect. rigid cable	10mm <sup>2</sup>

### Standards

European directive WEEE	concerned
-------------------------	-----------

### Use conditions

Operating temperature	-25...60 °C
Air humidity protection	95%
Storage/transport temperature	-40...80 °C