



MZ205

Under voltage release 48V DC

Product Datasheet

Main electrical features

Frequency	0/0 Hz
Type of supply voltage	DC

Voltage

Rated insulation voltage	4000 V
DC control voltage	48 V
Rated operational voltage in DC	48 V

Electric current

Acceptable current rating with AC1	50 mA
------------------------------------	-------

Power

Inrush power absorbed	2,4 VA
Total power loss under IN	2 W

Tripping

Performance voltage / Tripping at Ue	35/70 %
--------------------------------------	---------

Dimensions

Depth of installed product	68 mm
Width of installed product	17,5 mm

Installation, mounting

Tightening torque	1,2Nm
-------------------	-------

Connection

Connection cross-sect. rigid cable	10mm ²
Connection cross-sect. flexible conductor	6mm ²

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Storage temperature	-40 to 80 °C
Air humidity protection	95%