



MZ212

Over voltage release 230V AC

Product Datasheet

Main electrical features

Frequency	50/60 Hz
Type of supply voltage	AC
Rated operational voltage U _e	230 V

Voltage

Rated insulation voltage	500 V
Microcut resistance	70 ms

Power

Total power loss under I _N	0,7 W
---------------------------------------	-------

Tripping

Time of response when opening	7 s
Performance voltage / Tripping at U _e	110/180 %

Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	10000

Dimensions

Depth of installed product	68 mm
Height of installed product	87 mm
Width of installed product	17,5 mm

Installation, mounting

Tightening torque	1,2Nm
-------------------	-------

Connection

Connection cross-sect. rigid cable	10mm ²
Connection cross-sect. flexible conductor	6mm ²

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Storage temperature	-25 to 80 °C
Air humidity protection	85%