



ATA122088014

## T piece, ATEHA, 12x20, brown

### Product Datasheet

#### Architecture

Fixing mode	Clipped
-------------	---------

#### Functions

Overlapping	yes
Suitable for functional integrity according to DIN 4102-12	no

#### Configuration

Antibacterial treatment	no
Symmetrical	yes

#### Cover, door

Lid with softlip	No
------------------	----

#### Materials

Colour	brown
RAL colour	RAL 8014 - Sepia brown
Material	ABS
Material group	plastic
Type of surface treatment	untreated

#### Dimensions

Trunking height	12 mm
Length	20 mm
Trunking width	20 mm
Width	12 mm

#### Installation, mounting

Base punching	Without base punching
---------------	-----------------------

#### Accessories included

Accessory configuration	Moulded
-------------------------	---------

#### Equipment

With protective film	no
----------------------	----

#### Standards

Approvals	EN50085-2-1
European directive RoHs	voluntary compliance

#### Safety

Protection index IP	IP40
Halogen free	yes
Impact strength	IK07

**Use conditions**

Operating temperature	-5...60 °C
-----------------------	------------

**temperatur**

Ambient temperature	-5...60 °C
---------------------	------------