



slotted panel trunking BA7A 60x40, grey

Product Datasheet

Architecture

Flexible	no
----------	----

Configuration

Side wall configuration	Slotted
Self-extinguishing	yes

Electric current

Current leak stable	yes
---------------------	-----

Cover, door

Lid shape	loose
-----------	-------

Materials

Colour	stone grey
Material	PVC
Material group	plastic
Type of surface treatment	untreated

Dimensions

Trunking height	60 mm
Length	2000 mm
Trunking width	40 mm
Width of installed product	40 mm
Slot width	6 mm
Tongue width	6,5 mm

Installation, mounting

Base punching	EN 50085-2-3:1999
Fixing type	bottom punching

Cable

Number of wires 1,5 mm ² - 40% filling degree	66
Internal/useful cross section	1758 mm ²
Number of wires 2,5 mm ² - 40% filling degree	47
Number of wires 1,0 mm ² - 40% filling degree	91

Scope of delivery

Covers supplied with the product	yes
----------------------------------	-----

Standards

Approvals	EN50085-2-3
European directive RoHs	voluntary compliance
UL 94 classification	V0

BA7A60040

Safety

Halogen free	no
Fireproof classification	M1

temperatur

Ambient temperature	-5...60 °C
---------------------	------------