



slotted panel trunking BA7A 60x60, grey

Product Datasheet

Architecture

Flexible no

Configuration

Side wall configuration Slotted

Electric current

Current leak stable yes

Cover, door

Lid shape loose

Materials

Colour stone grey

Material PVC

Material group plastic

Type of surface treatment untreated

Dimensions

Length 2000 mm

Trunking height 60 mm

Trunking width 60 mm

Slot width 6 mm

Tongue width 6,5 mm

Installation, mounting

Fixing type bottom punching

Cable

Number of wires 1,5 mm² - 40% filling degree 102

Number of wires 2,5 mm² - 40% filling degree 73

Number of wires 1,0 mm² - 40% filling degree 142

Internal/useful cross section 2708 mm²

Standards

Approvals EN50085-2-3

European directive RoHs voluntary compliance

UL 94 classification V0

Safety

Halogen free no

Fireproof classification M1

BA7A60060

temperatur

Ambient temperature	-5 ... 60 °C
---------------------	--------------

Identification

Range name	tehalit BA7A
------------	--------------
