



WS100



Systo Socket 2P+T 16A screwless

Product Datasheet

Architecture

Type of pole	2P+T
Fixing mode	Recessed

Functions

Overvoltage protection	no
------------------------	----

Controls and indicators

Indicator lamp	no
With or without indicator	without

Connectivity

With USB charging socket	no
--------------------------	----

Main electrical features

Frequency	50/60 Hz
Nominal voltage	250 V

Capacity

Number of modules for WA	2
--------------------------	---

Cover, door

Lid shape	none
Interlockable	no

Power supply

Special power supply	No special power supply
----------------------	-------------------------

Materials

RAL colour	RAL 9010 - Pure white
Material	Polycarbonate (PC)
Surface appearance	satın finish
Type of surface treatment	mat

Dimensions

Depth of installed product	22,8 mm
Height of installed product	45 mm
Width of installed product	45 mm
Dimensions (LLxwwxhh)	45x45x37

Installation, mounting

Fixing type	Clipped
Mounting type	various

Connection

Connection cross-sect. rigid cable	1,5 / 2,5mm ²
Type of connection	quick connect
Phase pickup	L1

Equipment

On/Off switch	no
---------------	----

Standards

Approvals	NFC 61314
-----------	-----------

Safety

Protection index IP	IP2X
IK protection code against mechanical impacts	07

Identification

Range	systo
Version	F