



WS030



Systo 1M PB 10+1F w. light

Product Datasheet

Architecture

Type of order	push button
Type of control unit	Push button
Number of keys	1
Fixing mode	Recessed

Controls and indicators

Indicator lamp	as an accessory
----------------	-----------------

Main electrical features

Frequency	50/60 Hz
Nominal voltage	250 V

Capacity

Number of modules for WA	1
--------------------------	---

Materials

RAL colour	RAL 9010 - Pure white
Colour	white
Material	Polycarbonate (PC)
Material	polycarbonate
Type of surface treatment	mat

Dimensions

Depth of installed product	33 mm
Height of installed product	45 mm
Width of installed product	22 mm
Dimensions (LLxwxhh)	22.5x45x33

Installation, mounting

Fixing type	Clipped
-------------	---------

Connection

Type of connection	quick connect
Type of contacts	1NC+1NO

Standards

Approvals	EN 60669-1
-----------	------------

Safety

Protection index IP	IP31D
IK protection code against mechanical impacts	07
Glow wire test	according to NFC-20455 : 960°C

Use conditions

Storage temperature	-10 to 50 °C
---------------------	--------------

Identification

Composition	Mechanism with upper casing
Range	system
