



**Systo Socket 2P+T 16A for trunking Alu**

Product Datasheet

**Architecture**

Type of pole	2P+T
Fixing mode	screwed to base

**Functions**

Overvoltage protection	no
------------------------	----

**Controls and indicators**

Indicator lamp	no
With or without indicator	without

**Connectivity**

With USB charging socket	no
--------------------------	----

**Main electrical features**

Frequency	50/60 Hz
Nominal voltage	250 V

**Capacity**

Number of modules for WA	2
--------------------------	---

**Cover, door**

Interlockable	no
---------------	----

**Materials**

RAL colour	RAL 9006 - White aluminium
Material	Polycarbonate (PC)
Surface appearance	satın finish
Type of surface treatment	mat

**Dimensions**

Depth of installed product	43,5 mm
Height of installed product	45 mm
Width of installed product	67,5 mm
Dimensions (LLxwxh)	67.5x45x43.5mm

**Installation, mounting**

Fixing type	Clipped
Mounting type	various

**Connection**

Type of connection	quick connect
Phase pickup	L1

WS122T



WS121T



**Equipment**

---

On/Off switch	no
---------------	----

---

**Standards**

---

Approvals	NFC 61314
-----------	-----------

---

**Safety**

---

Protection index IP	IP2X
---------------------	------

---

IK protection code against mechanical impacts	07
---	----

---

**Identification**

---

Range	systo
-------	-------

---

Version	F
---------	---

---