




FL401A

Plain mounting plates

Description	Pack qty.	Art No.
Ste. mount. plate Orion.Plus 230x143 mm	1	FL401A
Ste. mount. plate Orion.Plus 280x193 mm	1	FL402A
Ste. mount. plate Orion.Plus 280x243 mm	1	FL403A
Ste. mount. plate Orion.Plus 330x243 mm	1	FL404A
Ste. mount. plate Orion.Plus 380x243 mm	1	FL405A
Ste. mount. plate Orion.Plus 380x343 mm	1	FL406A
Ste. mount. plate Orion.Plus 480x243 mm	1	FL407A
Ste. mount. plate Orion.Plus 480x343 mm	1	FL408A
Ste. moun. plate Orion.Plus 480x493 mm	1	FL510E
Ste. moun. plate Orion.Plus 480x743 mm	1	FL520E
Ste. moun. plate Orion.Plus 480x993 mm	1	FL530E
Ste. mount. plate Orion.Plus 630x343 mm	1	FL412A
Ste. mount. plate Orion.Plus 630x443 mm	1	FL413A
Ste. mount. plate Orion.Plus 780x443 mm	1	FL415A
mount.plate, orion.plus, 930x393x2	1	FL416A
mount.plate, orion.plus, 930x693x2	1	FL417A
mount.plate, orion.plus, 1230x693x2	1	FL419A
Ste. moun. plate Orion.Plus 1080x493 mm	1	FL512E
Ste. moun. plate Orion.Plus 780x743 mm	1	FL521E
Ste. moun. plate Orion.Plus 1080x743 mm	1	FL522E
Ste. moun. plate Orion.Plus 780x993 mm	1	FL531E
Ste. moun. plate Orion.Plus 1080x993 mm	1	FL532E
Ste. mount. plate Orion.Plus 480x443 mm	1	FL409A
Ste. mount. plate Orion.Plus 580x343 mm	1	FL410A
Ste. mount. plate Orion.Plus 580x543 mm	1	FL411A
Ste. mount. plate Orion.Plus 780x443mm	1	FL414A
Ste. moun. plate, Orion.Plus, 780x243 mm	1	FL501E
Ste. moun. plate Orion.Plus 1080x243 mm	1	FL502E
Ste. moun. plate Orion.Plus 780x493 mm	1	FL511E
mount.plate, orion.plus, 1230x543x2	1	FL418A



FL472A

Perforated mounting plates

Description	Pack qty.	Art No.
Ste. mount. plate Orion.Plus 280x193 mm	1	FL472A
Ste. mount. plate Orion.Plus 330x243 mm	1	FL473A
Ste. mount. plate Orion.Plus 480x243 mm	1	FL474A
Ste. mount. plate Orion.Plus 480x343 mm	1	FL475A
Ste. mount. plate Orion.Plus 630x343 mm	1	FL476A
Ste. mount. plate Orion.Plus 630x443 mm	1	FL477A
Ste. mount. plate Orion.Plus 780x543 mm	1	FL479A
mount.plate, orion.plus, 930x543x2	1	FL480A
mount.plate, orion.plus, 930x743x2	1	FL481A
mount.plate, orion.plus, 1230x743x2	1	FL483A
Ste. mount. plate Orion.Plus 780x443 mm	1	FL478A
mount.plate, orion.plus, 1230x543x2	1	FL482A

Insulated mounting plates

Description	Pack qty.	Art No.
Ins. mount. plate Orion.Plus 235x195 mm	2	FL422A
Ins. mount. plate Orion.Plus 285x245 mm	2	FL423A
Ins. mount. plate Orion.Plus 435x245 mm	2	FL424A
Ins. mount. plate Orion.Plus 435x345 mm	2	FL425A
Ins. moun. plate Orion.Plus 435x745 mm	1	FL560E
Ins. moun. plate Orion.Plus 435x995 mm	1	FL570E
Ins. moun. plate Orion.Plus 435x495 mm	2	FL550E
Ins. mount. plate Orion.Plus 585x345 mm	2	FL426A
Ins. mount. plate Orion.Plus 585x445 mm	2	FL427A
Ins. moun. plate Orion.Plus 735x245 mm	2	FL541E
Ins. mount. plate Orion.Plus 735x445 mm	2	FL428A
Ins. moun. plate Orion.Plus 735x495 mm	2	FL551E
Ins. mount. plate Orion.Plus 735x545 mm	2	FL429A
Ins. moun. plate Orion.Plus 735x745 mm	2	FL561E
Ins. moun. plate Orion.Plus 735x995 mm	2	FL571E
mount.plate, orion.plus, 885x545x6	2	FL430A
mount.plate, orion.plus, 545x745x6	2	FL431A
Ins. moun. plate Orion.Plus 1035x245 mm	2	FL542E
Ins. moun. plate Orion.Plus 1035x495 mm	2	FL552E
Ins. moun. plate Orion.Plus 1035x745 mm	2	FL562E
Ins. moun. plate Orion.Plus 1035x995 mm	2	FL572E
mount.plate, orion.plus, 1185x545x6	2	FL432A
mount.plate, orion.plus, 1185x745x6	2	FL433A



FL422A

Clips nuts and M5 screws

Description	Pack qty.	Art No.
Clips nut and screws, quadro, M5	25	UC969



UC969



FL541A

Sheet internal doors

Description	Pack qty.	Art No.
Steel counterd., Orion.Pl., H250 W200 mm	1	FL541A
Steel counterd., Orion.Pl., H300 W250 mm	1	FL542A
Steel counterd., Orion.Pl., H300 W300 mm	1	FL543A
Steel inner do., Orion+, 350x300 mm	1	FL544A
Steel counterd., Orion.Pl., H400 W300 mm	1	FL545A
Steel counterd., Orion.Pl., H400 W400 mm	1	FL546A
Steel inner do., Orion+, 500x300 mm	1	FL547A
Steel inner do., Orion+, 500x400 mm	1	FL548A
Steel inner door Orion.Plus 450x500 mm	1	FL590E
Steel inner door Orion.Plus 750x450 mm	1	FL600E
Steel counterd., Orion.Pl., H500 W500 mm	1	FL549A
Steel counterd., Orion.Pl., H600 W400 mm	1	FL550A
Steel inner do., Orion+, 650x400 mm	1	FL551A
Steel inner do., Orion+, 650x500 mm	1	FL552A
Steel counterd., Orion.Pl., H600 W600 mm	1	FL553A
Steel counterd., Orion.Pl., H800 W500 mm	1	FL554A
Steel inner do., Orion+, 800x600 mm	1	FL555A
Steel inner door Orion.Plus 450x250 mm	1	FL580E
Steel inner door Orion.Plus 750x250 mm	1	FL581E
Steel inner door Orion.Plus 1050x250 mm	1	FL582E
Steel inner door Orion.Plus 750x500 mm	1	FL591E
Steel inner door Orion.Plus 750x750 mm	1	FL601E
Steel inner door Orion.Plus 1050x500 mm	1	FL592E
Steel inner door Orion.Plus 1050x750 mm	1	FL602E
Steel counterd., Orion.Pl., H950 W600 mm	1	FL556A
Steel counterd., Orion.Pl., H950 W800 mm	1	FL557A
Steel counterd. Orion.Pl. H1250 W600 mm	1	FL558A
Steel counterd. Orion.Pl. H1250 W800 mm	1	FL559A



FL643A

Polyester internal doors

Description	Pack qty.	Art No.
Poly. inner do. Orion+ 350x300 mm	1	FL643A
Poly. inner do. Orion+ 500x300 mm	1	FL644A
Poly. inner do. Orion+ 500x400 mm	1	FL645A
Poly. inner do. Orion+ 650x400 mm	1	FL646A
Poly. inner do. Orion+ 650x500 mm	1	FL647A
Poly. inner do. Orion+ 800x600 mm	1	FL649A



FL461A

Functional uprights

Description	Pack qty.	Art No.
Functional uprights, Orion.Plus, H350 mm	1	FL461A
Functional uprights, Orion.Plus, H500 mm	1	FL462A
Functional uprights, Orion.Plus, H650 mm	1	FL463A
Functional uprights, Orion.Plus, H800 mm	1	FL465A
Functional uprights, Orion.Plus, H800 mm	1	FL466A
Functional uprights, Orion.Plus, H950 mm	1	FL467A
Functional uprights, Orion.Plus, H1250mm	1	FL468A



FL979A

Functional chassis

Description	Pack qty.	Art No.
Functional frame, Orion.Plus, 350x300 mm	1	FL979A
Chassis MCB, Orion.Plus, 24M 350x300mm	1	FL980A
Chassis MCB, Orion.Plus, 3x12M 500x300mm	1	FL981A
Chassis MCB, Orion.Plus, 3x18M 500x400mm	1	FL982A
Chassis MCB, Orion.Plus, 4x18M 650x400mm	1	FL983A

Sliding guides

Description	Pack qty.	Art No.
Sliding guides, Orion.Plus, L350 mm	5	FL672E



FL672E

Equipment kits

Description	Pack qty.	Art No.
Complete MCB kit Orion+ 2x12M 300x300mm	1	FL990C
Complete MCB kit Orion+ 2x12M 300x300mm	1	FL990A
Complete MCB kit Orion+ 3x12M 450x300mm	1	FL991A
Complete MCB kit Orion+ 4x18M 500x400mm	1	FL992A
Complete MCB kit Orion+ 3x23M 600x600mm	1	FL990B
Complete MCB kit Orion+ 3x37M 850x600mm	1	FL991B
Complete MCB kit Orion+ 4x18M 600x400mm	1	FL993A
Complete MCB kit Orion+ 4x24M 600x500mm	1	FL994A
Complete MCB kit Orion+ H750 W500 mm	1	FL995A
Complete MCB kit Orion+ 5x24M 750x600mm	1	FL996A
Complete MCB kit Orion+ 5x23M 600x900mm	1	FL992B
Complete MCB kit Orion+ 5x37M 850x900mm	1	FL993B
Compl. MCB kit Orion+ 6x26M H900 W600mm	1	FL997A
Compl. MCB kit Orion+ 6x37M H950 W800mm	1	FL998A
Complete MCB kit Orion+7x23M 600x1200mm	1	FL994B
Complete MCB kit Orion+7x37M 850x1200mm	1	FL995B
Compl. MCB kit Orion+ 8x26M H1200 W600mm	1	FL999A
MCB kit system, Orion.Plus, H1200 mm	1	FL000A
Kit system MCB, Orion.Plus, 150x300 mm	1	FL361A
Kit system MCB, Orion.Plus, 150x400 mm	1	FL362A
Kit system MCB, Orion.Plus, 150x500 mm	1	FL363A
Kit system MCB, Orion.Plus, 150x600 mm	1	FL364A
MCB kit, Orion.Plus, 150x800 mm	1	FL365A
Kit system MCB, Orion.Plus, 200x400 mm	1	FL366A
Kit system MCB, Orion.Plus, 200x500 mm	1	FL367A
Kit system MCB, Orion.Plus, 200x600 mm	1	FL368A
MCB kit, Orion.Plus, 200x800 mm	1	FL369A
Kit MCCB x160, Orion.Plus, 300x400 mm	1	FL371A
Kit MCCB x160, Orion.Plus, 300x500 mm	1	FL372A
Kit MCCB x160, Orion.Plus, 300x600 mm	1	FL373A
MCCB x250 kit Orion.Plus 300x800 mm	1	FL374A
Kit MCCB x250, Orion.Plus, 200x600 mm	1	FL380AH
MCCB x250 kit Orion.Plus 200x800 mm	1	FL381AH
Kit MCCB x250, Orion.Plus, 500x300 mm	1	FL391AH
Kit MCCB x250, Orion.Plus, 500x400 mm	1	FL392AH
Kit MCCB x250, Orion.Plus, 650x400 mm	1	FL393AH
Kit MCCB h630 Orion.Plus 650x400 mm	1	FL399AH




FL990C



FL311A

Partial mounting plates

Description	Pack qty.	Art No.
Fix moun. plate, Orion.Plus, 187x145 mm	1	FL311A
Fix moun. plate, Orion.Plus, 287x145 mm	1	FL312A
Fix moun. plate, Orion.Plus, 287x195 mm	1	FL322A
Fix moun. plate, Orion.Plus, 387x145 mm	1	FL313A
Fix moun. plate, Orion.Plus, 387x195 mm	1	FL323A
Fix moun. plate, Orion.Plus, 387x295 mm	1	FL333A
Fix moun. plate, Orion.Plus, 387x395 mm	1	FL343A
Adj. moun. plate, Orion.Plus, 234x145 mm	1	FL314A
Adj. ste. moun. plate Orion+ 604x195 mm	1	FL324A
Adj. ste. moun. plate Orion+ 334x145 mm	1	FL315A
Adj. ste. moun. plate Orion+ 334x195 mm	1	FL325A
Adj. ste. moun. plate Orion+ 334x295 mm	1	FL335A
Adj. ste. moun. plate Orion+ 334x395 mm	1	FL345A
Adj. ste. moun. plate Orion+ 404x145 mm	1	FL316A
Adj. ste. moun. plate Orion+ 404x195 mm	1	FL326A
Adj. ste. moun. plate Orion+ 404x295 mm	1	FL336A
Adj. ste. moun. plate Orion+ 404x395 mm	1	FL346A
Adj. ste. mount. plate Orion+ 145x354 mm	1	FL610E
Adj. ste. mount. plate Orion+ 195x354 mm	1	FL620E
Adj. ste. mount. plate Orion+ 295x354 mm	1	FL630E
Adj. ste. mount. plate Orion+ 395x354 mm	1	FL640E
Adj. ste. moun. plate Orion+ 604x145 mm	1	FL317A
Adj. ste. moun. plate Orion+ 604x195 mm	1	FL327A
Adj. ste. moun. plate Orion+ 604x295 mm	1	FL337A
Adj. ste. moun. plate Orion+ 604x395 mm	1	FL347A



FL711E

Plain front plates

Description	Pack qty.	Art No.
Front panel, Orion.Plus, 150x300 mm	1	FL711E
Front panel, Orion.Plus, 150x400 mm	1	FL712E
Front panel, Orion.Plus, 150x500 mm	1	FL713E
Front panel, Orion.Plus, 150x600 mm	1	FL714E
Front panel, Orion.Plus 150x800 mm	1	FL715E
Front panel, Orion.Plus, 50x400 mm	1	FL702E
Front panel, Orion.Plus, 50x500 mm	1	FL703E
Front panel, Orion.Plus, 50x600 mm	1	FL704E
Front panel, Orion.Plus 50x800 mm	1	FL705E
Front panel, Orion.Plus, 150x500 mm	1	FL710E
Front panel, Orion.Plus, 200x400 mm	1	FL722E
Front panel, Orion.Plus, 200x500 mm	1	FL723E
Front panel, Orion.Plus, 200x600 mm	1	FL724E
Front panel, Orion.Plus 200x800 mm	1	FL725E
Front panel, Orion.Plus, 300x500 mm	1	FL733E
Front panel, Orion.Plus 300x600 mm	1	FL734E
Front panel, Orion.Plus 300x800 mm	1	FL735E



FL500A

Settable DIN rails

Description	Pack qty.	Art No.
Clamp DIN rail, Orion.Plus, W400 mm	1	FL500A
Clamp DIN rail, Orion.Plus, W500 mm	1	FL501A
Clamp DIN rail, Orion.Plus, W600 mm	1	FL502A
Clamp DIN rail, Orion.Plus, W800 mm	1	FL503A
Clamp DIN rail, Orion.Plus, W500 mm	1	FL500E

Support for earth and neutral terminals

Description	Pack qty.	Art No.
Clamp bracket, Orion.Plus, W300 mm	1	FL492A
Clamp bracket, Orion.Plus, W400 mm	5	FL493A
Clamp bracket, Orion.Plus, W500 mm	1	FL494A
Clamp bracket, Orion.Plus, W600 mm	1	FL495A
Clamp bracket, Orion.Plus, W800 mm	5	FL496A



FL492A

Mounting plate bracket

Description	Pack qty.	Art No.
Fixing bracket, moun. plate, Orion.Plus	10	FL450A



FL450A

Cable ducts

Description	Pack qty.	Art No.
Cable trunking 25x60mm 2xL2000mm	1	FL70Z
Cable trunking 40x60mm 2xL2000mm	1	FL71Z



UC916

Cable guide


Description	Pack qty.	Art No.
Transmission clamp, universN, 20 pcs.	1	UZ25V1
Transmission clamp, universN, 20 pcs.	1	UZ25V2



UZ25V1

Fixing bracket

Description	Pack qty.	Art No.
Adaptor, universN, double, 20pcs	1	UZ01V1



UZ01V1



UT50C

Vertical cover

Description	Pack qty.	Art No.
Cover trunking, universN, 78x31mm, 2m	20	UT50C



FL871Z

Blanking strip

Description	Pack qty.	Art No.
Blanking strips, Quadro.Plus, 4 pieces	1	FL871Z



FL210Z

Ventilators

Description	Pack qty.	Art No.
Fan, quadro.system, 20W 57 m3/h	1	FL210Z
Fan, quadro.system, 20W 115 m3/h	1	FL212Z
Fan, quadro.system, 32W 240 m3/h	1	FL214Z
Fan, quadro.system, 67W 520m3/h	1	FL216Z



FL220Z

Air vent

Description	Pack qty.	Art No.
Air grill, quadro.system, 150x150 mm	1	FL220Z
Air grill, quadro.system, 250x250 mm	1	FL224Z
Air grill, quadro.system, 325x325 mm	1	FL226Z



FL230Z

Filters

Description	Pack qty.	Art No.
Fan filter quadro.system 20 W 150x150 mm	1	FL230Z
Fan filter quadro.system 32 W 250x250 mm	1	FL234Z
Fan filter quadro.system 67 W 325x325 mm	1	FL236Z

Heater supply

Description	Pack qty.	Art No.
Heaters, quadro.system, 15 W 230 V AC/DC	1	FL252Z
Heaters, quadro.system, 30 W 230 V AC/DC	1	FL253Z
Heaters, quadro.system, 45 W 230 V AC/DC	1	FL254Z
Heaters, quadro.system, 80 W 230 V AC/DC	1	FL255Z
Heaters, quadro.system, 150 W 230 V AC/D	1	FL256Z



FL252Z

Thermostat

Description	Pack qty.	Art No.
Thermostat, quadro.system, 10 A 230 V AC	1	FL258Z
Thermostat, quadro.system, 10 A 230 V AC	1	FL259Z



FL258Z