

**Base and lid depth 25 mm**

Description	Pack qty.	Art No.
HNG 25025/0 Grey 7035 Trunking	36	HNG2502507035 B

HNG2502507035B

**Base and lid depth 40 mm**


Description	Pack qty.	Art No.
HNG 37025/0 Grey 7035 Trunking	48	HNG3702507035 B
HNG 37037/0 Grey 7035 Trunking	32	HNG3703707035 B
HNG 37050/0 Grey 7035 Trunking	40	HNG3705007035 B

HNG3702507035B

**Base and lid depth 50 mm**

Description	Pack qty.	Art No.
HNG 50025/0 Grey 7035 Trunking	48	HNG5002507035 B
HNG 50037/0 Grey 7035 Trunking	40	HNG5003707035 B
HNG 50050/0 Grey 7035 Trunking	48	HNG5005007035 B
HNG 50075/0 Grey 7035 Trunking	20	HNG5007507035 B
HNG 50100/0 Grey 7035 Trunking	24	HNG5010007035 B
HNG 50125/0 Grey 7035 Trunking	18	HNG5012507035 B

HNG5002507035B

**Base and lid depth 75 mm**

Description	Pack qty.	Art No.
HNG 75037/0 Grey 7035 Trunking	40	HNG7503707035 B
HNG 75050/0 Grey 7035 Trunking	20	HNG7505007035 B
HNG 75075/0 Grey 7035 Trunking	16	HNG7507507035 B
HNG 75100/0 Grey 7035 Trunking	16	HNG7510007035 B
HNG 75125/0 Grey 7035 Trunking	12	HNG7512507035 B

HNG7503707035B



HN370503

Clip

Description	Pack qty.	Art No.
HN 37050/3 Retaining clip	50	HN370503
HN 50050/3 Retaining clip	50	HN500503
HN 50075/3 Retaining clip	50	HN500753
HN 50100/3 Retaining clip	50	HN501003
HN 50125/3 Retaining clip	50	HN501253
HN 75050/3 Retaining clip	50	HN750503
HN 75075/3 Retaining clip	50	HN750753
HN 75100/3 Retaining clip	50	HN751003
HN 75125/3 Retaining clip	50	HN751253