

1 pole, Curve B, 6000 A / 10 kA

Description	Pack qty.	Art No.
MCB 1P 6/10kA B-6A 1M	12	NE106A
MCB 1P 6/10kA B-10A 1M	12	NE110A
MCB 1P 6/10kA B-16A 1M	12	NE116A
MCB 1P 6/10kA B-20A 1M	12	NE120A
MCB 1P 6/10kA B-25A 1M	12	NE125A
MCB 1P 6/10kA B-32A 1M	12	NE132A
MCB 1P 6/10kA B-40A 1M	12	NE140A
MCB 1P 6/10kA B-50A 1M	12	NE150A
MCB 1P 6/10kA B-63A 1M	12	NE163A

2 pole, Curve B, 6000 A / 10 kA

Description	Pack qty.	Art No.
MCB 2P 6/10kA B-6A 2M	6	NE206A
MCB 2P 6/10kA B-10A 2M	6	NE210A
MCB 2P 6/10kA B-16A 2M	6	NE216A
MCB 2P 6/10kA B-20A 2M	6	NE220A
MCB 2P 6/10kA B-25A 2M	6	NE225A
MCB 2P 6/10kA B-32A 2M	6	NE232A
MCB 2P 6/10kA B-40A 2M	6	NE240A
MCB 2P 6/10kA B-50A 2M	6	NE250A
MCB 2P 6/10kA B-63A 2M	6	NE263A

3 pole, Curve B, 6000 A / 10 kA

Description	Pack qty.	Art No.
MCB 3P 6/10kA B-6A 3M	4	NE306A
MCB 3P 6/10kA B-10A 3M	4	NE310A
MCB 3P 6/10kA B-16A 3M	4	NE316A
MCB 3P 6/10kA B-20A 3M	4	NE320A
MCB 3P 6/10kA B-25A 3M	4	NE325A
MCB 3P 6/10kA B-32A 3M	4	NE332A
MCB 3P 6/10kA B-40A 3M	4	NE340A
MCB 3P 6/10kA B-50A 3M	4	NE350A
MCB 3P 6/10kA B-63A 3M	4	NE363A

4 pole, Curve B, 6000 A / 10 kA

Description	Pack qty.	Art No.
MCB 4P 6/10kA B-6A 4M	3	NE406A
MCB 4P 6/10kA B-10A 4M	3	NE410A
MCB 4P 6/10kA B-16A 4M	3	NE416A
MCB 4P 6/10kA B-20A 4M	3	NE420A
MCB 4P 6/10kA B-25A 4M	3	NE425A
MCB 4P 6/10kA B-32A 4M	3	NE432A
MCB 4P 6/10kA B-40A 4M	3	NE440A
MCB 4P 6/10kA B-50A 4M	3	NE450A
MCB 4P 6/10kA B-63A 4M	3	NE463A

1 pole, Curve C, 6000 A / 10 kA

Description	Pack qty.	Art No.
MCB 1P 6/10kA C-0.5A 1M	12	NF100A
MCB 1P 6/10kA C-1A 1M	12	NF101A
MCB 1P 6/10kA C-2A 1M	12	NF102A
MCB 1P 6/10kA C-3A 1M	12	NF103A
MCB 1P 6/10kA C-4A 1M	12	NF104A
MCB 1P 6/10kA C-6A 1M	12	NF106A
MCB 1P 6/10kA C-10A 1M	12	NF110A
MCB 1P 6/10kA C-16A 1M	12	NF116A
MCB 1P 6/10kA C-20A 1M	12	NF120A
MCB 1P 6/10kA C-25A 1M	12	NF125A
MCB 1P 6/10kA C-32A 1M	12	NF132A
MCB 1P 6/10kA C-40A 1M	12	NF140A
MCB 1P 6/10kA C-50A 1M	12	NF150A
MCB 1P 6/10kA C-63A 1M	12	NF163A



NF106A

2 pole, Curve C, 6000 A / 10 kA

Description	Pack qty.	Art No.
MCB 2P 6/10kA C-0.5A 2M	6	NF200A
MCB 2P 6/10kA C-1A 2M	6	NF201A
MCB 2P 6/10kA C-2A 2M	6	NF202A
MCB 2P 6/10kA C-3A 2M	6	NF203A
MCB 2P 6/10kA C-4A 2M	6	NF204A
MCB 2P 6/10kA C-6A 2M	6	NF206A
MCB 2P 6/10kA C-10A 2M	6	NF210A
MCB 2P 6/10kA C-16A 2M	6	NF216A
MCB 2P 6/10kA C-20A 2M	6	NF220A
MCB 2P 6/10kA C-25A 2M	6	NF225A
MCB 2P 6/10kA C-32A 2M	6	NF232A
MCB 2P 6/10kA C-40A 2M	6	NF240A
MCB 2P 6/10kA C-50A 2M	6	NF250A
MCB 2P 6/10kA C-63A 2M	6	NF263A

3 pole, Curve C, 6000 A / 10 kA

Description	Pack qty.	Art No.
MCB 3P 6/10kA C-0.5A 3M	4	NF300A
MCB 3P 6/10kA C-1A 3M	4	NF301A
MCB 3P 6/10kA C-2A 3M	4	NF302A
MCB 3P 6/10kA C-3A 3M	4	NF303A
MCB 3P 6/10kA C-4A 3M	4	NF304A
MCB 3P 6/10kA C-6A 3M	4	NF306A
MCB 3P 6/10kA C-10A 3M	4	NF310A
MCB 3P 6/10kA C-16A 3M	4	NF316A
MCB 3P 6/10kA C-20A 3M	4	NF320A
MCB 3P 6/10kA C-25A 3M	4	NF325A
MCB 3P 6/10kA C-32A 3M	4	NF332A
MCB 3P 6/10kA C-40A 3M	4	NF340A
MCB 3P 6/10kA C-50A 3M	4	NF350A
MCB 3P 6/10kA C-63A 3M	4	NF363A



NF340A



NF410A

4 pole, Curve C, 6000 A / 10 kA

Description	Pack qty.	Art No.
MCB 4P 6/10kA C-0.5A 4M	3	NF400A
MCB 4P 6/10kA C-1A 4M	3	NF401A
MCB 4P 6/10kA C-2A 4M	3	NF402A
MCB 4P 6/10kA C-3A 4M	3	NF403A
MCB 4P 6/10kA C-4A 4M	3	NF404A
MCB 4P 6/10kA C-6A 4M	3	NF406A
MCB 4P 6/10kA C-10A 4M	3	NF410A
MCB 4P 6/10kA C-16A 4M	3	NF416A
MCB 4P 6/10kA C-20A 4M	3	NF420A
MCB 4P 6/10kA C-25A 4M	3	NF425A
MCB 4P 6/10kA C-32A 4M	3	NF432A
MCB 4P 6/10kA C-40A 4M	3	NF440A
MCB 4P 6/10kA C-50A 4M	3	NF450A
MCB 4P 6/10kA C-63A 4M	3	NF463A