

# Cable ducting system

	<b>Page</b>
tehalit.BA7 cable ducting system	3
tehalit.BA7 blue cable ducting system	5
tehalit.HA7 halogen free slotted trunking	6
tehalit.HNG halogen free slotted trunking in PPO	7
tehalit.VK-flex halogen free flexible slotted trunking	8



**Base and lid depth 25 mm**

Description	Pack qty.	Art No.
slottet panel trunking BA7A 25x25, grey	50	<b>BA7A25025</b>
slottet panel trunking BA7A 25x40, grey	48	<b>BA7A25040</b>

BA7A25025



**Base and lid depth 40 mm**

Description	Pack qty.	Art No.
slottet panel trunking BA7A 40x25, grey	48	<b>BA7A40025</b>
slottet panel trunking BA7A 40x40, grey	50	<b>BA7A40040</b>
slottet panel trunking BA7A 40x60, grey	40	<b>BA7A40060</b>
slottet panel trunking BA7A 40x80, grey	30	<b>BA7A40080</b>
slottet panel trunking BA7A 40x100, grey	20	<b>BA7A40100</b>

BA7A40025



**Base and lid depth 60 mm**

Description	Pack qty.	Art No.
slottet panel trunking BA7A 60x25, grey	60	<b>BA7A60025</b>
slottet panel trunking BA7A 60x40, grey	40	<b>BA7A60040</b>
slottet panel trunking BA7A 60x60, grey	24	<b>BA7A60060</b>
slottet panel trunking BA7A 60x80, grey	20	<b>BA7A60080</b>
slottet panel trunking BA7A 60x100, grey	16	<b>BA7A60100</b>
slottet panel trunking BA7A 60x120, grey	12	<b>BA7A60120</b>


BA7A60025



**Base and lid depth 80 mm**

Description	Pack qty.	Art No.
slottet panel trunking BA7A 80x25, grey	20	<b>BA7A80025</b>
slottet panel trunking BA7A 80x40, grey	20	<b>BA7A80040</b>
slottet panel trunking BA7A 80x60, grey	20	<b>BA7A80060</b>
slottet panel trunking BA7A 80x80, grey	12	<b>BA7A80080</b>
slottet panel trunking BA7A 80x100, grey	12	<b>BA7A80100</b>
slottet panel trunking BA7A 80x120, grey	16	<b>BA7A80120</b>

BA7A80025



**Base and lid depth 100 mm**

Description	Pack qty.	Art No.
slottet panel trunking BA7A 100x60, grey	16	<b>BA7A100060</b>
slottet panel trunking BA7A 100x80, grey	16	<b>BA7A100080</b>
slottet panel trunking BA7A 100x100, grey	12	<b>BA7A100100</b>

BA7A100060

**Lids separate**

Description	Pack qty.	Art No.
slotted trunking lid PVC BA7 25x25mm sg	28	<b>BA70252K</b>
slotted trunking lid PVC BA7 25x40mm sg	28	<b>BA70402K</b>
slot trunk lid h 40/60/80 BA7 w=25 sg	28	<b>BA70252</b>
slot trunk lid h 40/60/80 BA7 w=40 sg	28	<b>BA70402</b>
slotted trunking lid PVC BA7 w=60 sg	20	<b>BA70602</b>
slotted trunking lid PVC BA7 w=80 sg	20	<b>BA70802</b>
slotted trunking lid PVC BA7 w=100 sg	12	<b>BA71002</b>
slotted trunking lid PVC BA7 w=120 sg	12	<b>BA71202</b>

BA70252K





**Base and lid depth 25 mm**

Description	Pack qty.	Art No.
slottet panel trunking BA7 25x25, blue	50	<b>BA725025BL</b>

BA725025BL



**Base and lid depth 40 mm**

Description	Pack qty.	Art No.
slottet panel trunking BA7 40x25, blue	48	<b>BA740025BL</b>
slottet panel trunking BA7 40x40, blue	50	<b>BA740040BL</b>
slottet panel trunking BA7 40x60, blue	40	<b>BA740060BL</b>

BA740025BL



**Base and lid depth 60 mm**

Description	Pack qty.	Art No.
slottet panel trunking BA7 60x25, blue	60	<b>BA760025BL</b>
slottet panel trunking BA7 60x40, blue	40	<b>BA760040BL</b>
slottet panel trunking BA7 60x60, blue	24	<b>BA760060BL</b>

BA760025BL



**Base and lid depth 80 mm**

Description	Pack qty.	Art No.
slottet panel trunking BA7 80x25, blue	20	<b>BA780025BL</b>
slottet panel trunking BA7 80x60, blue	20	<b>BA780060BL</b>
slottet panel trunking BA7 80x100, blue	12	<b>BA780100BL</b>

BA780025BL

**Base and lid depth 25 mm**

Description	Pack qty.	Art No.
slotted panel trunking HA7 25x25, lg	50	<b>HA725025</b>



HA725025

**Base and lid depth 40 mm**


Description	Pack qty.	Art No.
slotted panel trunking HA7 40x25, lg	48	<b>HA740025</b>
slotted panel trunking HA7 40x40, lg	50	<b>HA740040</b>
slotted panel trunking HA7 40x60, lg	40	<b>HA740060</b>



HA740025

**Base and lid depth 60 mm**


Description	Pack qty.	Art No.
slotted panel trunking HA7 60x25, lg	60	<b>HA760025</b>
slotted panel trunking HA7 60x40, lg	40	<b>HA760040</b>
slotted panel trunking HA7 60x60, lg	24	<b>HA760060</b>
slotted panel trunking HA7 60x80, lg	20	<b>HA760080</b>
slotted panel trunking HA7 60x100, lg	16	<b>HA760100</b>
slotted panel trunking HA7 60x120, lg	12	<b>HA760120</b>



HA760025

**Base and lid depth 80 mm**

Description	Pack qty.	Art No.
slotted panel trunking HA7 80x40, lg	20	<b>HA780040</b>
slotted panel trunking HA7 80x60, lg	20	<b>HA780060</b>
slotted panel trunking HA7 80x80, lg	12	<b>HA780080</b>
slotted panel trunking HA7 80x100, lg	12	<b>HA780100</b>
slotted panel trunking HA7 80x120, lg	16	<b>HA780120</b>



HA780040

**Lids separate**

Description	Pack qty.	Art No.
slot trunk lid h 40/60/80 HA7 w=25 lg	28	<b>HA70252</b>
slot trunk lid PC/ABS HA7 25x25mm lg	28	<b>HA70252K</b>
slot trunk lid h 40/60/80 HA7 w=40 lg	28	<b>HA70402</b>
slotted trunking lid PC/ABS HA7 w=60 lg	20	<b>HA70602</b>
slotted trunking lid PC/ABS HA7 w=80 lg	20	<b>HA70802</b>
slotted trunking lid PC/ABS HA7 w=100 lg	12	<b>HA71002</b>
slotted trunking lid PC/ABS HA7 w=120 lg	12	<b>HA71202</b>



HA70252



**Base and lid depth 25 mm**

Description	Pack qty.	Art No.
HNG 25025/0 Grey 7035 Trunking	36	<b>HNG2502507035 B</b>

HNG2502507035B



**Base and lid depth 40 mm**

Description	Pack qty.	Art No.
HNG 37025/0 Grey 7035 Trunking	48	<b>HNG3702507035 B</b>
HNG 37037/0 Grey 7035 Trunking	32	<b>HNG3703707035 B</b>
HNG 37050/0 Grey 7035 Trunking	40	<b>HNG3705007035 B</b>


HNG3702507035B



**Base and lid depth 50 mm**

Description	Pack qty.	Art No.
HNG 50025/0 Grey 7035 Trunking	48	<b>HNG5002507035 B</b>
HNG 50037/0 Grey 7035 Trunking	40	<b>HNG5003707035 B</b>
HNG 50050/0 Grey 7035 Trunking	48	<b>HNG5005007035 B</b>
HNG 50075/0 Grey 7035 Trunking	20	<b>HNG5007507035 B</b>
HNG 50100/0 Grey 7035 Trunking	24	<b>HNG5010007035 B</b>
HNG 50125/0 Grey 7035 Trunking	18	<b>HNG5012507035 B</b>

HNG5002507035B



**Base and lid depth 75 mm**

Description	Pack qty.	Art No.
HNG 75037/0 Grey 7035 Trunking	40	<b>HNG7503707035 B</b>
HNG 75050/0 Grey 7035 Trunking	20	<b>HNG7505007035 B</b>
HNG 75075/0 Grey 7035 Trunking	16	<b>HNG7507507035 B</b>
HNG 75100/0 Grey 7035 Trunking	16	<b>HNG7510007035 B</b>
HNG 75125/0 Grey 7035 Trunking	12	<b>HNG7512507035 B</b>

HNG7503707035B



**Clip**

Description	Pack qty.	Art No.
HN 37050/3 Retaining clip	50	<b>HN370503</b>
HN 50050/3 Retaining clip	50	<b>HN500503</b>
HN 50075/3 Retaining clip	50	<b>HN500753</b>
HN 50100/3 Retaining clip	50	<b>HN501003</b>
HN 50125/3 Retaining clip	50	<b>HN501253</b>
HN 75050/3 Retaining clip	50	<b>HN750503</b>
HN 75075/3 Retaining clip	50	<b>HN750753</b>
HN 75100/3 Retaining clip	50	<b>HN751003</b>
HN 75125/3 Retaining clip	50	<b>HN751253</b>

HN370503

**VK-flex 10 without adhesive tape**

Description	Pack qty.	Art No.
M 5690 Grey VK-Flex	40	<b>M5690</b>



M5690



**VK-flex 20 without adhesive tape**

Description	Pack qty.	Art No.
M 5691 Grey VK Flex	40	<b>M5691</b>



M5691



**VK-flex 30 without adhesive tape**

Description	Pack qty.	Art No.
Slotted trunking VK-flex30 grey	40	<b>M5692</b>



M5692



**VK-flex 40 without adhesive tape**

Description	Pack qty.	Art No.
Slotted trunking VK-flex40 grey	40	<b>M5693</b>



M5693







**VK-flex 10 with adhesive tape**

Description	Pack qty.	Art No.
L 2212 Grey VK Flex	40	<b>L2212</b>

L2212



**VK-flex 20 with adhesive tape**

Description	Pack qty.	Art No.
L 2222 Grey VK Flex	40	<b>L2222</b>

L2222



**VK-flex 30 with adhesive tape**

Description	Pack qty.	Art No.
L 2232 Grey VK Flex	40	<b>L2232</b>

L2232



**VK-flex 40 with adhesive tape**

Description	Pack qty.	Art No.
L 2242 Grey VK Flex	40	<b>L2242</b>

L2242

