



FL109A

Steel encl., Orion.Plus, 500x300x160 mm

Product Datasheet

Architecture

Fixing mode Wall mounting

Compatibility

Suitable for lightning protection no

Electric current

Rated current 630 A

Cover, door

Material thickness cover 1,5 mm

Type of door closing lock with male triangular wrench

Interlockable yes

Cover type Closed (plain)

Door leave single

Door quantity 1

Cover type Door

Transparent cover or door no

Materials

Colour RAL 7035

Colour light grey

RAL colour RAL 7035 - Light grey

Material Steel

Type of surface treatment powder-coated

Dimensions

Insertion depth 160 mm

Depth of installed product 160 mm

Internal depth 160 mm

Height of installed product 500 mm

Width of installed product 300 mm

Width in division units 10

Thickness of sidewall material 1,2 mm

Installation, mounting

Suitable for outdoor use no

Accessories included

Mounting plate included no

With lock yes

Equipment

Number of rows	3
Number of keys	1
Number of openings for flange plates	2
Extension possible	yes

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	>IK10
Protection index IP	IP65
Protection class	isol.class I
Fire resistance	-