



FWB52S

FWB encl., univers, IP44,800x550x161mm, QC

Product Datasheet

Architecture

Fixing mode flush-mounting/surface-mounting/section make

Functions

With a pipe-in lead yes

Compatibility

Compatible with DIN rail mounting yes

Electric current

Rated current 125 A

Cover, door

Type of door closing hinged pattern handle

Number of keylock of the door 1

Door locking without

Door leave single

Door quantity 1

Cover type Cover

Transparent cover or door no

Materials

Copper weight of the product 0,081 kg

Colour white

RAL colour RAL 9010 - Pure white

Material sheet steel

Dimensions

Depth of installed product 161 mm

Internal depth 161 mm

Height of installed product 800 mm

Width of installed product 550 mm

Width in division units 12

Thickness of sidewall material 2 mm

Installation, mounting

Suitable for outdoor use no

Connection

Number of conduit inlets 8

Accessories included

Mounting plate included no

With lock no

Equipment

Number of rows	10
Quantity of section in width	2
Number of keys	1
Quantity of rails	10
Can be accessorized	yes
Number of openings for flange plates	4

Standards

European directive WEEE	concerned
Protection class according to IEC-61140	II

Safety

IK protection code against mechanical impacts	09
Protection index IP	IP44
Protection class	isol.class II
Impact strength	IK09