



BA7A80080

slotted panel trunking BA7A 80x80, grey

Product Datasheet

Architecture

Flexible no

Configuration

Side wall configuration Slotted

Self-extinguishing yes

Electric current

Current leak stable yes

Cover, door

Lid shape loose

Materials

Colour stone grey

Material PVC

Material group plastic

Type of surface treatment untreated

Dimensions

Trunking height 80 mm

Length 2000 mm

Trunking width 80 mm

Slot width 6 mm

Tongue width 6,5 mm

Installation, mounting

Base punching EN 50085-2-3:1999

Fixing type bottom punching

Cable

Number of wires 1,5 mm² - 40% filling degree 206

Internal/useful cross section 5198 mm²

Number of wires 2,5 mm² - 40% filling degree 148

Number of wires 1,0 mm² - 40% filling degree 287

Scope of delivery

Covers supplied with the product yes

Standards

Approvals EN50085-2-3

European directive RoHs voluntary compliance

UL 94 classification V0

Safety

Halogen free	no
Fireproof classification	M1

temperatur

Ambient temperature	-5 ... 60 °C
---------------------	--------------
