

# h3 ACBs

Air Circuit Breakers are used to protect low voltage installations from 800 to 6300A. These devices feature a high level of performance in a reduced volume.





HXA001H

## Accessories

| Description                                | Pack qty. | Art No. |
|--|-----------|---------|
| Shunt trip 24V DC (x/P160-x/P250-x/P630)   | 1         | HXA001H |
| Shunt trip 48V DC (x/P160-x/P250-x/P630)   | 1         | HXA002H |
| SHT 100-120V AC (x/P160-x/P250-x/P630)     | 1         | HXA003H |
| SHT 200-240V AC (x/P160-x/P250-x/P630)     | 1         | HXA004H |
| SHT 380-450V AC (x/P160-x/P250-x/P630)     | 1         | HXA005H |
| UVR 24V DC (x/P160-x/P250-x/P630)          | 1         | HXA011H |
| UVR 100-120V AC (x/P160-x/P250-x/P630)     | 1         | HXA013H |
| UVR 200-240V AC (x/P160-x/P250-x/P630)     | 1         | HXA014H |
| AX contact 1NO+NC 250VAC (x/P160...x/P630) | 1         | HXA021H |
| AL contact 1NO+NC 250VAC (x/P160...x/P630) | 1         | HXA024H |
| AX low lvl. 1NO+NC 125VAC(x/P160...x/P630) | 1         | HXA025H |
| AL low lvl. 1NO+NC 125VAC(x/P160...x/P630) | 1         | HXA026H |
| Direct rotary handle x160                  | 1         | HXA030H |
| Extended rotary handle x160                | 1         | HXA031H |
| Padlock (x160-P160-x250-P250-x630)         | 1         | HXA039H |
| UVR delayed 24V DC (x160-P160-x250-P250)   | 1         | HXA051H |
| UVR delayed 110-120VAC (x/P 160-x/P 250)   | 1         | HXA053H |
| UVR delayed 220-240VAC (x/P 160-x/P 250)   | 1         | HXA054H |
| UVR delayed 380-450V AC (x/P160-x/P250)    | 1         | HXA055H |
| Direct rotary handle x250                  | 1         | HXB030H |
| Extended rotary handle x250                | 1         | HXB031H |
| Motor operator x250 24V DC                 | 1         | HXB040H |
| Motor operator x250 230-240VAC             | 1         | HXB042H |
| Interlocking wire type x250                | 1         | HXB065H |
| Interlock front cover x250                 | 1         | HXB066H |
| Elec. interlock Motor A (x/P/h 250)        | 1         | HXB068H |
| Elec.interlock MotB(x/P/h250-h400..1000)   | 1         | HXB069H |
| Interlock cable 1m(P160-x/h/P250..1000)    | 1         | HXB070H |
| Interlock cable 1.5m(P160-x/h250..1000)    | 1         | HXB071H |
| Shunt trip Release 24V DC(h250...1000)     | 1         | HXC001H |
| Shunt trip Release 48V DC(h250...1000)     | 1         | HXC002H |
| SHT trip Release 100-120VAC(h250...1000)   | 1         | HXC003H |
| SHT trip Release 200-240VAC(h250...1000)   | 1         | HXC004H |
| SHT trip Release 380-450VAC(h250...1000)   | 1         | HXC005H |
| Shunt trip Release 110V DC(h250...1000)    | 1         | HXC008H |
| Undervolt. Release 24V DC(h250...630)      | 1         | HXC011H |
| Undervolt. Release 100-120VAC(h250..630)   | 1         | HXC013H |
| Undervolt. Release 100-120VDC(h250..630)   | 1         | HXC018H |
| Undervolt. Release 200-240VDC(h250..630)   | 1         | HXC019H |
| AX contact 1NO+1NC 230VAC(h250...1600)     | 1         | HXC021H |
| Alarm contact 1NO+1NC 230V(h250...1600)    | 1         | HXC024H |
| Aux low lvl 1NO+NC 125V AC(h250...1600)    | 1         | HXC025H |
| AL contact low level 1NO+NC(h250...1600)   | 1         | HXC026H |
| Direct rotary handle H250                  | 1         | HXC030H |
| Extended rotary handle H250                | 1         | HXC031H |
| Padlock H250                               | 1         | HXC039H |
| Motor operator h250 24V DC                 | 1         | HXC040H |
| Motor operator h250 230-240VAC             | 1         | HXC042H |
| UVR delayed h250-h630 24V DC               | 1         | HXC051H |
| UVR delayed 500ms h250 110-120V AC         | 1         | HXC053H |
| UVR delayed h250-h630 220-240V AC          | 1         | HXC054H |
| UVR delayed h250-h630 380-415V AC          | 1         | HXC055H |
| Interlocking wire type H250                | 1         | HXC065H |
| Interlock front cover h250                 | 1         | HXC066H |
| Motor operator h400-h630 24-48V DC         | 1         | HXD040H |
| UVR delayed h400-h630 4P 24VDC             | 1         | HXD051H |
| UVR delayed h400-h630 4P 110-120VAC        | 1         | HXD053H |
| UVR delayed h400-h630 4P 220-240VAC        | 1         | HXD054H |
| UVR delayed h400-h630 4P 380-415VAC        | 1         | HXD055H |
| Interlock front cover h630                 | 1         | HXD066H |
| Elec.interl Motor A h/P400-630-800-1000    | 1         | HXD068H |
| UVR 24VDC (h800-h1000-h1600)               | 1         | HXE011H |
| UVR 110-120VAC (h800-h1000-h1600)          | 1         | HXE013H |
| UVR 220-240VAC (h800-h1000-h1600)          | 1         | HXE014H |
| UVR 380-415VAC (h800-h1000-h1600)          | 1         | HXE015H |
| UVR 100-120 V DC (h800-h1000-h1600)        | 1         | HXE018H |
| UVR 200-240 V DC (h800-h1000-h1600)        | 1         | HXE019H |
| Direct rotary handle H800-H1000            | 1         | HXE030H |

| Description                           | Pack qty. | Art No.        |
|---------------------------------------|-----------|----------------|
| Extended rotary handle H800-H1000     | 1         | <b>HXE031H</b> |
| Motor operator h800-h1000 24-48V DC   | 1         | <b>HXE040H</b> |
| Motor operator H800-H1000 100-240VAC  | 1         | <b>HXE042H</b> |
| UVR delayed h800-h1600 3P 24VDC       | 1         | <b>HXE051H</b> |
| UVR delayed h800-h1600 3P 110-120VAC  | 1         | <b>HXE053H</b> |
| UVR delayed h800-h1000 3P 220-240VAC  | 1         | <b>HXE054H</b> |
| UVR delayed h800-h1600 3P 380-415VAC  | 1         | <b>HXE055H</b> |
| Interlocking wire type H800-H1000     | 1         | <b>HXE065H</b> |
| Interlock front cover h1000           | 1         | <b>HXE066H</b> |
| Direct rotary handle H1250-H1600      | 1         | <b>HXF030H</b> |
| Extended rotary handle H1250-H1600    | 1         | <b>HXF031H</b> |
| Padlock H1250-H1600                   | 1         | <b>HXF039H</b> |
| Motor operator h1250-h1600 24V DC     | 1         | <b>HXF040H</b> |
| Motor operator H1250-H1600 200-230VAC | 1         | <b>HXF042H</b> |
| UVR delayed h800-h1600 4P 24VDC       | 1         | <b>HXF051H</b> |
| UVR delayed h800-h1600 4P 110-120VAC  | 1         | <b>HXF053H</b> |
| UVR delayed h1600 4P 220-240VAC       | 1         | <b>HXF054H</b> |
| UVR delayed h800-h1600 4P 380-415VAC  | 1         | <b>HXF055H</b> |