

# Blocks and terminals

	<b>Page</b>
Junction blocks	3
Brass terminals	6
Bases for brass terminals, rails for connection blocks and terminals	8



K018

**Junction blocks**


Description	Pack qty.	Art No.
Branch terminal, universZ, 1x25-4 x16mm <sup>2</sup>	20	<b>K018</b>
Branch terminal, universZ, 2p, 1x25 <sup>2</sup> -4 x16 <sup>2</sup>	10	<b>K023</b>
Branch terminal, universZ, 4p, 1x25 <sup>2</sup> -4 x16 <sup>2</sup>	5	<b>K024</b>
Branch terminal, universZ, 5p, 1x25 <sup>2</sup> -4 x16 <sup>2</sup>	5	<b>K025</b>
Main line branch term. 1p. 1x35mm <sup>2</sup> -4x25mm <sup>2</sup>	4	<b>K037</b>



KR95P

**Junction terminals**

Description	Pack qty.	Art No.
DIN rail terminal 25-95mm <sup>2</sup>	1	<b>KR95P</b>
DIN rail terminal 35-150mm <sup>2</sup>	1	<b>KR15P</b>



K010

**Connecting bars**

Description	Pack qty.	Art No.
Connect.clamp, universZ, 2x5x4mm	20	<b>K010</b>



K085

**Grounding connection**

Description	Pack qty.	Art No.
Grounding connection-separate-wedges	10	<b>K085</b>




KXA02LH

**Phase terminals**

Description	Pack qty.	Art No.
Feed-through terminal -phase, 2,5mm <sup>2</sup>	100	<b>KXA02LH</b>
Feed-through terminal-phase, 4mm <sup>2</sup>	100	<b>KXA04LH</b>
Feed-through terminal -phase, 10mm <sup>2</sup>	50	<b>KXA10L</b>
Feed-through terminal-phase, 16mm <sup>2</sup>	50	<b>KXA16L</b>
Feed-through terminal-phase, 35mm <sup>2</sup>	20	<b>KXA35L</b>
Feed-through terminal-phase , 70mm <sup>2</sup>	20	<b>KXB70LH</b>
Feed-through terminal-phase, 150mm <sup>2</sup>	10	<b>KXB150LH</b>

### Neutral terminals

Description	Pack qty.	Art No.
Feed-through terminal-N, 2,5mm <sup>2</sup>	100	<b>KXA02NH</b>
Feed-through terminal-N, 4mm <sup>2</sup>	100	<b>KXA04NH</b>
Feed-through terminal -N, 10mm <sup>2</sup>	50	<b>KXA10N</b>
Feed-through terminal-N, 16mm <sup>2</sup>	50	<b>KXA16N</b>
Feed-through terminal-N, 35mm <sup>2</sup>	20	<b>KXA35N</b>
Feed-through terminal-N, 70mm <sup>2</sup>	20	<b>KXB70NH</b>
Feed-through terminal-N, 150mm <sup>2</sup>	10	<b>KXB150NH</b>



KXA02NH

### Earth terminals PE

Description	Pack qty.	Art No.
Earth terminal, 2,5mm <sup>2</sup>	100	<b>KXA02E</b>
Earth terminal, 4mm <sup>2</sup>	100	<b>KXB04E</b>
Earth terminal 10mm <sup>2</sup>	50	<b>KXA10E</b>
Earth terminal, 16mm <sup>2</sup>	50	<b>KXA16E</b>
Earth terminal, 35mm <sup>2</sup>	20	<b>KXB35E</b>
Earth terminal, 70mm <sup>2</sup>	20	<b>KXB70E</b>



KXA02E

### Insulated end caps

Description	Pack qty.	Art No.
Endplate for KXA02LH, KXA04LH	10	<b>KWE01G</b>
Endplate for KXA10L, KXA16L	10	<b>KWE04G</b>
Endplate for KXA35L	10	<b>KWE03G</b>



KWE01G

### Insulated end stops

Description	Pack qty.	Art No.
End bracket until 35mm <sup>2</sup>	100	<b>KWB01</b>
End bracket until 150qmm <sup>2</sup>	100	<b>KWB02</b>




KWB01

### Bridging bars for screw junction terminals

Description	Pack qty.	Art No.
Jumper insulated, 2,5mm <sup>2</sup> , 10-way	10	<b>KWJ02B10</b>
Jumper insulated, 4mm <sup>2</sup> , 10-way	10	<b>KWJ04B10</b>
Jumper insulated, 10mm <sup>2</sup> , 10-way	10	<b>KWJ10B10</b>



KWJ02B10



**Marking strips**

Description	Pack qty.	Art No.
Marking Clip - Box (0-9)	1	<b>KWL001</b>
Marking strips 1-100	1	<b>KWL002</b>
Marking strips 101-200	1	<b>KWL003</b>
Marking strip L1, L2, L3, N, PE	1	<b>KWL004</b>

KWL001

### Brass terminals with base neutral

Description	Pack qty.	Art No.
Brass terminal, 4x10mm <sup>2</sup> 3x16mm <sup>2</sup> , N	50	<b>KM07N</b>
Brass terminal, 5x10mm <sup>2</sup> 5x16mm <sup>2</sup> , N	20	<b>KM10A</b>
Brass terminal, 5x10mm <sup>2</sup> 5x16mm <sup>2</sup> , N	20	<b>KM11N</b>
Brass terminal, 8x10mm <sup>2</sup> 2x16mm <sup>2</sup> , N	20	<b>KM10N</b>
Brass terminal, 7x10mm <sup>2</sup> 6x16mm <sup>2</sup> , N	20	<b>KM13N</b>
Brass terminal, 1x25mm <sup>2</sup> 8x10mm <sup>2</sup> 8x16mm <sup>2</sup> , N	20	<b>KM17N</b>
Brass terminal, 1x25 <sup>2</sup> 13x10 <sup>2</sup> 11x16 <sup>2</sup> , N	20	<b>KM25N</b>
Feed-through terminal-N, 6mm <sup>2</sup>	100	<b>KXA06NH</b>



KM07N

### Brass terminals with base earth


Description	Pack qty.	Art No.
Brass terminal, 4x10mm <sup>2</sup> 3x16mm <sup>2</sup> , Earth	50	<b>KM07E</b>
Brass terminal, 5x10mm <sup>2</sup> 5x16mm <sup>2</sup> , Earth	20	<b>KM10B</b>
Brass terminal, 5x10mm <sup>2</sup> 5x16mm <sup>2</sup> , Earth	20	<b>KM11E</b>
Brass terminal, 8x10mm <sup>2</sup> 2x16mm <sup>2</sup> , Earth	20	<b>KM10E</b>
Brass terminal, 7x10mm <sup>2</sup> 6x16mm <sup>2</sup> , Earth	20	<b>KM13E</b>
Brass terminal, 1x25 <sup>2</sup> 5x10 <sup>2</sup> 5x16 <sup>2</sup> , Earth	20	<b>KM11B</b>
Brass terminal, 1x25 <sup>2</sup> 8x10 <sup>2</sup> 8x16 <sup>2</sup> , Earth	20	<b>KM17E</b>
Brass terminal, 1x25 <sup>2</sup> 13x10 <sup>2</sup> 11x16 <sup>2</sup> , Earth	20	<b>KM25E</b>
Earth terminal, 6mm <sup>2</sup>	100	<b>KXB06E</b>



KM07E

### Brass terminals with base phase

Description	Pack qty.	Art No.
Brass terminal, 2x10mm <sup>2</sup> /2x16mm <sup>2</sup> , Phase	50	<b>KM04L</b>
Brass terminal, 4x10mm <sup>2</sup> 4x16mm <sup>2</sup> , Phase	20	<b>KM08L</b>
Brass terminal, 4x10mm <sup>2</sup> 3x16mm <sup>2</sup> , Phase	50	<b>KM07L</b>
Brass terminal, 5x10mm <sup>2</sup> - 5x16mm <sup>2</sup>	20	<b>KM10C</b>
Brass terminal, 7x10mm <sup>2</sup> 4x16mm <sup>2</sup> , Phase	20	<b>KM11L</b>
Brass terminal, 8x10mm <sup>2</sup> 2x16mm <sup>2</sup> , Phase	20	<b>KM10L</b>
Multi tier terminal -phase, 2,5mm <sup>2</sup>	100	<b>KXA02LX</b>
Multi tier terminal-phase, 4mm <sup>2</sup>	100	<b>KXA04LX</b>
Earth terminal , multi tier, 4mm <sup>2</sup>	100	<b>KXB04EX</b>



KM04L

### Brass terminals without base

Description	Pack qty.	Art No.
Brass terminal, 30mm, 2x10mm <sup>2</sup> - 2x16mm <sup>2</sup>	10	<b>K140</b>
Brass terminal, 49mm, 4x10mm <sup>2</sup> - 3x16mm <sup>2</sup>	10	<b>K142</b>
Brass terminal, 67mm, 5x10mm <sup>2</sup> - 5x16mm <sup>2</sup>	10	<b>K143</b>
Brass terminal, 73mm, 6x10mm <sup>2</sup> - 5x16mm <sup>2</sup>	10	<b>K144</b>
Brass terminal, 8x10mm <sup>2</sup> - 2x16mm <sup>2</sup>	10	<b>K145</b>
Brass terminal, 85mm, 7x10mm <sup>2</sup> - 6x16mm <sup>2</sup>	10	<b>K148</b>
Brass terminal, 85mm, 1x25mm <sup>2</sup> - 5x10/16mm <sup>2</sup>	10	<b>K151</b>
TERM.STRIP 121MM 1X25-4X16-12X10MM <sup>2</sup>	10	<b>K156</b>
Brass terminal 1x25mm <sup>2</sup> -11x16mm <sup>2</sup> -13x10mm <sup>2</sup>	10	<b>K158</b>
Brass terminal 1x25mm <sup>2</sup> - 8x16mm <sup>2</sup> -31x10mm <sup>2</sup>	10	<b>K159</b>
Term.strip 482mm 78x10/16mm	10	<b>K160F</b>
Term.strip 992mm 163x10/16mm	10	<b>K162F</b>



K140

### Bases

Description	Pack qty.	Art No.
Mounting base f. brass terminals, blue	10	<b>KZ012</b>
Mounting base f. brass terminals, green	10	<b>KZ013</b>
Mounting base f. brass terminals, brown	10	<b>KZ014</b>



KZ012



KXB04F5

**Fuse terminal**

Description	Pack qty.	Art No.
G-Fuse terminal(5x20), 4mm <sup>2</sup>	50	<b>KXB04F5</b>



KWE25G

**Endplate**

Description	Pack qty.	Art No.
Endplate for KXA02VB, KXA02LX	10	<b>KWE25G</b>
Endplate for KXA04VB, KXA04LX	10	<b>KWE26G</b>

## Flat bar supports for terminal strips



Description	Pack qty.	Art No.
#NV	50	<b>A08900</b>

A089

## Pinch carriers



Description	Pack qty.	Art No.
Terminal carrier, Univers, L250 mm	10	<b>UT91A</b>

UT91A


## Brass terminal support



Description	Pack qty.	Art No.
FLAT BAR 12X2MM LENGTH 2 M.	10	<b>A09000</b>

A090

## Rail fixing clips



Description	Pack qty.	Art No.
Fixing spring f.DIN rail 10pcs, 20mm wide	10	<b>KZ060F</b>
Fixing spring f. DIN rail, 10mm wide	50	<b>KZ061</b>

KZ060F

## Symmetrical rails



Description	Pack qty.	Art No.
SYMMETRICAL DIN RAIL 2M	20	<b>A08800</b>
SYMMETRICAL DIN RAIL 10MM 2M	20	<b>A09800</b>
SYMMETRICAL DIN RAIL 15MM 2M	10	<b>A09900</b>

A09900






**Asymmetrical rails**

Description	Pack qty.	Art No.
Perforated rail DIN, Venezia, 15x2000 mm	10	<b>A099E</b>
Perforated DIN-rail, Venezia, 15x2000 mm	10	<b>A099B</b>
ASYMMETRICAL DIN RAIL 2M	10	<b>A05000</b>

A099E



**DIN rail**

Description	Pack qty.	Art No.
Profile rail, Venezia, 15x2000 mm	10	<b>A099C</b>

A099C



**Special nuts**

Description	Pack qty.	Art No.
Nut for profile rail DIN, Venezia, M6	25	<b>A099D</b>

A099D



**Screw**

Description	Pack qty.	Art No.
Tapping screw 3,5x12,0 +/- PZ1	1	<b>KZ062</b>

KZ062