



Enclosures
depth 260 mm
delivered without plinth



Enclosures
depth 260 mm and 400 mm
delivered with plinth of 150 mm



enclosures height with top and bottom or plinth	internal equipment height	enclosures width:			enclosures width:		(685 mm useful)	
		(685 mm useful) 700 mm total	pair of sides	plinth 150 mm	(435 mm useful) 450 mm total d. 260 mm d. 400 mm	(685 mm useful) 700 mm total d. 260 mm d. 400 mm		
510 mm	450 mm	FM200	FM400	FM450	-	-		
660 mm	600 mm	FM201	FM401	FM450	-	-		
810 mm	750 mm	FM202	FM402	FM450	-	-		
960 mm	900 mm	FM203	FM403	FM450	-	-		
1110 mm	1050 mm	FM204	FM404	FM450	-	-		
1260 mm	1200 mm	FM205	FM405	FM450	-	-		
1410 mm	1350 mm	FM206	FM406	FM450	-	-		
1710 mm	1500 mm	-	-	-	FM107	FM117	FM207	FM217
1860 mm	1650 mm	-	-	-	FM108	FM118	FM208	FM218
2010 mm	1800 mm	-	-	-	FM109	FM119	FM209	FM219
vertical association kit		FM 630+ UC890	-	-	-	-	FM630 possible	
horizontal association kit		FM 635+ UC890	-	-	FM 635+ UC890	FM 635+ UC890	FM 635+ UC890	-


Enclosures
depth 260 mm and
400 mm delivered with
plinth of 150 mm



Side panels



**Busbar compartment
and cable sleeve**



Doors



Enclosures		Side panels		Busbar compartment and cable sleeve		Doors			transparent doors:		functionnal uprights
(885 mm useful)	900 mm total	pair of sides		for enclosure: width		full doors:			width	width	d. 400 mm
d. 260 mm	d. 400 mm	d. 260 mm	d. 400 mm	d. 260 mm	d. 400 mm	width	width	width	width	width	
						435 mm	685 mm	885 mm	685 mm	885 mm	
-	-	-	-	-	-	-	FM530	-	FM540	-	-
-	-	-	-	-	-	-	FM531	-	FM541	-	-
-	-	-	-	-	-	-	FM532	-	FM542	-	-
-	-	-	-	-	-	-	FM533	-	FM543	-	-
-	-	-	-	-	-	-	FM534	-	FM544	-	-
-	-	-	-	-	-	-	FM535	-	FM545	-	-
-	-	-	-	-	-	-	FM536	-	FM546	-	-
FM307	FM317	FM407	FM417	FM427	FM437	FM517	FM537	FM557	FM547	FM567	FM477
FM308	FM318	FM408	FM418	FM428	FM438	FM518	FM538	FM558	FM548	FM568	FM478
FM309	FM319	FM409	FM419	FM429	FM439	FM519	FM539	FM559	FM549	FM569	FM479
-	-	-	-	-	-	-	-	-	-	-	-
FM635+ UC890	-	-	-	-	-	-	-	-	-	-	-