



WNC035

cubyko Key SW 2 positions wall M grey

Product Datasheet

Architecture

Type of control unit	Key
Number of keys	1
Fixing mode	Screwed

Controls and indicators

Indicator lamp	no
- No	

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 AX
---------------	-------

Materials

Colour	complete grey
RAL colour	RAL 7011 - Iron grey
Material	polypropylène
Material	Polypropylen
Type of surface treatment	mat

Dimensions

Depth of installed product	74 mm
Height of installed product	75 mm
Dimensions (LLxwwxhh)	76x76x80
Width of installed product	75 mm

Installation, mounting

Mounting type	surface
---------------	---------

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of connection	quick connect

Equipment

- without lighting (cannot be illuminated)

Standards

Approvals	EN 60669-1
-----------	------------

Safety

IK protection code against mechanical impacts	07
Protection index IP	IP55

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C

Identification

Range	cubyko
Composition	Complete installation with frame
