



FK110

**hauteur 1900 mm**

Description	Cond.	Référence
Porte, FK, opaque, 1900x600x400mm	1	<b>FK110</b>
Porte, FK, opaque, 1900x800x400mm	1	<b>FK120</b>
Porte, FK, opaque, 1900x1000x400mm	1	<b>FK130</b>
Porte, FK, opaque, 1900x600x500mm	1	<b>FK111</b>
Porte, FK, opaque, 1900x800x500mm	1	<b>FK121</b>
Porte, FK, opaque, 1900x1000x500mm	1	<b>FK131</b>



FK113

**hauteur 2100 mm**

Description	Cond.	Référence
Porte, FK, opaque, 2100x600x400mm	1	<b>FK113</b>
Porte, FK, opaque, 2100x800x400mm	1	<b>FK123</b>
Porte, FK, opaque, 2100x1000x400mm	1	<b>FK133</b>
Porte, FK, opaque, 2100x600x500mm	1	<b>FK114</b>
Porte, FK, opaque, 2100x800x500mm	1	<b>FK124</b>
Porte, FK, opaque, 2100x1000x500mm	1	<b>FK134</b>