



FWB31S

FWB encl., univers, IP44,500x300x161mm, QC

Product Datasheet

Architecture

Fixing mode flush-mounting/surface-mounting/section make

Functions

With a pipe-in lead yes

Configuration

Module with terminals

Compatibility

Compatible with DIN rail mounting yes

Electric current

Rated current 125 A

Cover, door

Type of door closing hinged pattern handle

Number of keylock of the door 1

Cover type With Notch

Door locking without

Door leave single

Door quantity 1

Cover type Door

Transparent cover or door no

Materials

Copper weight of the product 0,036 kg

Colour white

RAL colour RAL 9010 - Pure white

Material sheet steel

Dimensions

Depth of installed product 165 mm

Internal depth 156 mm

Height of installed product 500 mm

Installation height 500 mm

Width of installed product 300 mm

Width in division units 12

Thickness of sidewall material 1 mm

Installation, mounting

Suitable for outdoor use no

Connection

Number of conduit inlets	4
--------------------------	---

Accessories included

Mounting plate included	no
With lock	no

Equipment

Number of rows	3
Quantity of section in width	1
Number of keys	1
Quantity of rails	3
Can be accessorized	yes
Number of openings for flange plates	2
Extension possible	yes

Standards

European directive WEEE	concerned
Protection class according to IEC-61140	II

Safety

IK protection code against mechanical impacts	09
Protection index IP	IP44
Protection class	isol.class II
Impact strength	IK09