



VZ020D

Press. bala. screw joint, vector, IP66, M20

Product Datasheet

Functions

| | |
|---------------------------------------|--------|
| Strain relief possibility | yes |
| Suitable for nominal thread metric/PG | 0 / 20 |

Materials

| | |
|---------------------------|---------------|
| Colour | light grey |
| Material | plastic |
| Material quality | thermoplastic |
| Type of surface treatment | untreated |

Mecanic features

| | |
|-------------|--------|
| Thread type | Metric |
|-------------|--------|

Dimensions

| | |
|-----------------------|-------|
| thread gradient | 1,5 |
| Screw head size in mm | 27 mm |

Connection

| | |
|----------------|---------|
| Clamping range | 6-13 mm |
|----------------|---------|

Equipment

| | |
|----------|----|
| Screened | no |
|----------|----|

Standards

| | |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

Safety

| | |
|----------------------------------|------|
| Protection index IP | IP65 |
| Halogen free | yes |
| Compliant Ex-Zone dust | none |
| Safe use in explosive atmosphere | no |
| For Ex-zone gas | no |

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -25...40 °C |
|-----------------------|-------------|