



VZ025D

**Press.bala.screw joint, vector, IP66, M25**

Product Datasheet

**Functions**

Strain relief possibility	yes
Suitable for nominal thread metric/PG	0 / 25

**Materials**

Colour	light grey
Material	plastic
Material quality	thermoplastic
Type of surface treatment	untreated

**Mecanic features**

Thread type	Metric
-------------	--------

**Dimensions**

thread gradient	1,5
Screw head size in mm	32 mm

**Connection**

Clamping range	9-17 mm
----------------	---------

**Equipment**

Screened	no
----------	----

**Standards**

European directive WEEE	not concerned
-------------------------	---------------

**Safety**

Protection index IP	IP65
Halogen free	yes
Compliant Ex-Zone dust	none
Safe use in explosive atmosphere	no
For Ex-zone gas	no

**Use conditions**

Operating temperature	-25...40 °C
-----------------------	-------------