



FL254B

**Poly. enc. Orion+ gl. d. 350x300x160 mm**

Product Datasheet

**Architecture**

Fixing mode Wall mounting

**Compatibility**

Suitable for lightning protection no

**Electric current**

Rated current 630 A

**Cover, door**

Type of door closing lock with male triangular wrench

Interlockable yes

Number of keylock of the door 2

Cover type Closed (plain)

Door leave single

Door material Plastic

Door quantity 1

Door transparent material Plastic

Cover type Door

Transparent cover or door yes

**Materials**

Colour RAL 7035

Colour light grey

RAL colour RAL 7035 - Light grey

Material glas reinforced polyester

Type of surface treatment untreated

**Dimensions**

Depth of installed product 160 mm

Internal depth 160 mm

Height of installed product 350 mm

Width of installed product 300 mm

Width in division units 12

Thickness of sidewall material 3 mm

**Installation, mounting**

Suitable for outdoor use yes

**Accessories included**

Mounting plate included no

With lock yes

**Equipment**

Number of rows	2
Number of keys	2
Quantity of rails	2

**Standards**

Approvals	BS EN 62208
European directive WEEE	not concerned

**Safety**

IK protection code against mechanical impacts	IK08
Protection index IP	IP66
Protection class	isol.class II