



FL322B

Poly. floor encl. Orion+ 1200x600x300 mm

Product Datasheet

Architecture

Fixing mode surface-mounting

Compatibility

Suitable for lightning protection no

Electric current

Rated current 630 A

Cover, door

Type of door closing lock with male triangular wrench

Cover type With Notch

Door leave single

Cover type Door

Transparent cover or door yes

Materials

Colour RAL 7035

Colour light grey

RAL colour RAL 7035 - Light grey

Material plastic

Type of surface treatment powder-coated

Dimensions

Insertion depth 300 mm

Depth of installed product 300 mm

Internal depth 300 mm

Height of installed product 1200 mm

Width of installed product 600 mm

Thickness of sidewall material 1,5 mm

Installation, mounting

Suitable for outdoor use yes

Accessories included

Mounting plate included no

With lock yes

Equipment

Number of rows 7

Quantity of section in width 1

Number of keys 1

Extension possible yes

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	>IK10
---	-------

Protection index IP	IP65
---------------------	------

Protection class	isol.class II
------------------	---------------

Fire resistance	-
-----------------	---
