



FL344B

Poly. double enc. Orion+ 1750x600x300 mm

Product Datasheet

Architecture

Fixing mode surface-mounting

Compatibility

Compatible with DIN rail mounting yes

Electric current

Rated current 630 A

Cover, door

Type of door closing lock with male triangular wrench

Cover type With Notch

Door locking with key

Cover type Door

Transparent cover or door yes

Materials

Colour RAL 7035

Colour light grey

RAL colour RAL 7035 - Light grey

Material plastic

Dimensions

Insertion depth 300 mm

Depth of installed product 300 mm

Internal depth 300 mm

Height of installed product 1750 mm

Width of installed product 600 mm

Width in division units 23

Installation, mounting

Suitable for outdoor use yes

Accessories included

Mounting plate included no

With lock yes

Equipment

Number of rows 9

Quantity of section in width 1

Number of keys 2

Can be accessorized yes

Extension possible yes

Safety

Protection index IP

IP65
