



FL532B

**Poly. floor encl. Orion+ 1200x1100x300 m**

Product Datasheet

**Architecture**

Fixing mode Floor fastening

**Compatibility**

Suitable for lightning protection no

**Electric current**

Rated current 630 A

**Cover, door**

Type of door closing lock with male triangular wrench

Cover type Closed (plain)

Door leave single

Cover type Door

Transparent cover or door yes

**Materials**

Colour RAL 7035

Colour light grey

RAL colour RAL 7035 - Light grey

Material plastic

Type of surface treatment powder-coated

**Dimensions**

Insertion depth 300 mm

Depth of installed product 300 mm

Internal depth 300 mm

Height of installed product 1200 mm

Width of installed product 1100 mm

Thickness of sidewall material 1,5 mm

**Installation, mounting**

Suitable for outdoor use yes

**Accessories included**

Mounting plate included no

With lock yes

**Equipment**

Number of rows 7

Number of keys 2

Extension possible yes

**Standards**

---

European directive WEEE	not concerned
-------------------------	---------------

---

**Safety**

---

IK protection code against mechanical impacts	>IK10
---	-------

---

Protection index IP	IP65
---------------------	------

---

Protection class	isol.class II
------------------	---------------

---

Fire resistance	-
-----------------	---

---