



HBD401H

RCD add on h400 4P 400A I_{dn} adj

Product Datasheet

Architecture

Number of poles 4 P

Main electrical features

Rated operational voltage U_e 220 / 415 V

Frequency 50/60 Hz

Voltage

Rated insulation voltage 500 V

Rated impulse withstand voltage 6000 V

Electric current

Rated residual operating current 30 mA / 100 mA / 300 mA / 1 A / 3 A / 6 A

Rated current 400 A

Power

Total power loss under I_N 24 W

Power loss per pole at I_n 8 W

Connection

Connection cross-sect. rigid cable 240 mm²

Settings

Rated fault current adjustable no

Delay adjustable yes

Time delay of residual current 0 / 0,06 / 0,15 / 0,3 / 0,5 / 1 s

Standards

Standard text IEC 60947-2

European directive WEEE concerned

Safety

Residual current type A