



MZ205

Under voltage release 48V DC

Product Datasheet

Functions

Switch-off delay	no
Switch-on delay	no

Main electrical features

Type of supply voltage	DC
------------------------	----

Voltage

Rated insulation voltage	4000 V
DC control voltage	48 V
Rated operational voltage in DC	48 V

Electric current

Acceptable current rating with AC1	50 mA
------------------------------------	-------

Power

Inrush power absorbed	2,4 VA
Total power loss under I _N	2 W

Tripping

Performance voltage / Tripping at U _e	35 / 70 %
--	-----------

Dimensions

Depth of installed product	68 mm
Width of installed product	17,5 mm

Installation, mounting

Tightening torque	1,2Nm
360° product mounting position	yes

Connection

Connection cross-sect. flexible conductor	6mm ²
Connection cross-sect. rigid cable	10mm ²

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-25...60 °C
Air humidity protection	95%
Storage/transport temperature	-40...80 °C