



SU212

Bell 12V

Product Datasheet

Architecture

Fixing mode DIN rail type O (symmetrical)

Functions

- Sound signal : type D - duration of intermittent operation : 5s / ON et 15s / OFF

Main electrical features

Rated operational voltage Ue 8 / 12 V

Type of supply voltage AC

Electric current

Operating current 0,33 A

Rated current 0,33 A

Frequency

Frequency 50 to 0 Hz

Power

Power consumed 5 VA

Total power loss under IN 5 W

Materials

Material polyamide

Dimensions

Depth of installed product 65 mm

Height of installed product 80 mm

Width of installed product 18 mm

Connection

Connection cross-sect. flexible conductor 4mm²

Connection cross-sect. rigid cable 6mm²

Equipment

Noise level 85 dB

Standards

European directive WEEE concerned

Safety

Protection index IP IP20

Use conditions

Operating temperature	-10...40 °C
Storage/transport temperature	-25...60 °C
