



SU214

## Buzzer 12V

Product Datasheet

### Architecture

Fixing mode DIN rail type O (symmetrical)

### Functions

- Sound signal : type D - duration of intermittent operation : 5s / ON et 15s / OFF

### Main electrical features

Rated operational voltage Ue 8 / 12 V

Type of supply voltage AC

### Electric current

Operating current 0,33 A

Rated current 0,33 A

### Power

Power consumed 4 VA

Total power loss under IN 4 W

### Materials

Material polyamide

### Dimensions

Depth of installed product 65 mm

Height of installed product 80 mm

Width of installed product 18 mm

### Connection

Connection cross-sect. flexible conductor 4mm<sup>2</sup>

Connection cross-sect. rigid cable 6mm<sup>2</sup>

### Equipment

Noise level 78 dB

HVAC-control no

### Standards

European directive WEEE concerned

### Safety

Protection index IP IP20

### Use conditions

Operating temperature -10...40 °C

Storage/transport temperature -25...60 °C