



SU215

Buzzer 230V

Product Datasheet

Architecture

Fixing mode	DIN rail type O (symmetrical)
-------------	-------------------------------

Functions

- Sound signal : type D - duration of intermittent operation : 5s / ON et 15s / OFF

Main electrical features

Rated operational voltage Ue	230 V
Type of supply voltage	AC

Electric current

Operating current	0,03 A
Rated current	0,03 A

Frequency

Frequency	50 to 0 Hz
-----------	------------

Power

Power consumed	6,5 VA
Total power loss under IN	6,5 W

Materials

Material	polyamide
----------	-----------

Dimensions

Depth of installed product	65 mm
Height of installed product	80 mm
Width of installed product	18 mm

Connection

Connection cross-sect. flexible conductor	4mm ²
Connection cross-sect. rigid cable	6mm ²

Equipment

Noise level	78 dB
HVAC-control	no

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-10...40 °C
Storage/transport temperature	-25...60 °C
