




ATA125039010



External corner, ATEHA, 12x50, pure white

Product Datasheet

Architecture

Fixing mode Clipped

Functions

Overlapping yes

Suitable for functional integrity according to DIN 4102-12 no

Configuration

Antibacterial treatment no

Symmetrical yes

Connectivity

Trunking coupling without coupler

Cover, door

Lid with softlip No

Materials

Colour pure white

RAL colour RAL 9010 - Pure white

Material ABS

Material group plastic

Type of surface treatment untreated

Dimensions

Trunking height 13 mm

Length 26,5 mm

Trunking width 52 mm

Installation, mounting

Base punching Without base punching

Settings

Angle range 83 / 140 °

Accessories included

Accessory configuration Moulded

Equipment

With protective film no

Standards

Approvals EN50085-2-1

European directive RoHs voluntary compliance

Safety

Protection index IP	IP40
Halogen free	yes
Impact strength	IK07

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

temperatur

Ambient temperature	-5...60 °C
---------------------	------------