



Trunking lid SL20055 cherry

Product Datasheet

Cover, door

Lid mounting	External
Lid with softlip	No
Lid width	20 mm

Materials

Colour	cherry
Material	PVC
Material group	plastic
Type of surface treatment	Effect finishing

Dimensions

Trunking height	55 mm
Length	2000 mm
Trunking width	20 mm

Equipment

With carpet border	no
With protective film	yes

Standards

Approvals	CE
European directive RoHs	voluntary compliance

Safety

Protection index IP	IP40
Halogen free	no
Impact strength	IK07

Use conditions

Operating temperature	5...60 °C
-----------------------	-----------

temperatur

Ambient temperature	5...60 °C
---------------------	-----------

SL200552D4

