



Insulated busbar 2P prong 16mm² 57M

Product Datasheet

Architecture

Number of poles 2 P

Compatibility

Intended for the compatible references Modular devices

Main electrical features

Rated operational voltage Ue 230 / 400 V

Voltage

Max operating voltage 400 V

Rated impulse withstand voltage 4 kV

Electric current

Rated current 80 A

Power supply

Number of phases for the power supply 2 phases

Materials

Colour stone grey

Dimensions

Length 1000 mm

Pitch 17,8 mm

Fixation distance in module steps 2

Installation, mounting

Suitable to a device with an auxiliary no

Connection

Connection cross-sect. rigid cable 16mm²

Suitable for product with neutral busbar yes

Connector type busbar prong

Type of connection with screw

Equipment

Number of appliances to build in 28

Standards

European directive WEEE concerned

Use conditions

Insulated yes

KB280B