




AKA181250ELN



floortrack AKA181250ELN

Product Datasheet

Configuration

Antibacterial treatment	no
Self-adhesive	no

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	8
--	---

Cover, door

Lid with softlip	No
------------------	----

Materials

Colour	aluminium
Material	Aluminium
Material group	aluminium

Dimensions

Trunking height	18 mm
Length	2000 mm
Standard length	2000 mm
Trunking width	125 mm
Width of installed product	125 mm

Equipment

Number of fix dividers	1
Compartment quantity	2
Number of channels	2
With anti-slip layer	no

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP30
Halogen free	yes
Impact strength	IK08

Weight

Max. load	15 t
-----------	------