



M66639010



endcap LFH 40060, pure white

Product Datasheet

Architecture

Fixing mode Clamping and screwable

Functions

Overlapping no
 Suitable for functional integrity according to DIN 4102-12 no

Configuration

Antibacterial treatment no

Compatibility

Product compatibility LF

Connectivity

Trunking coupling without coupler

Materials

Colour pure white
 RAL colour RAL 9010 - Pure white
 Material PC-ABS
 Material group plastic
 Type of surface treatment untreated

Dimensions

Trunking height 40 mm
 Trunking width 60 mm

Equipment

With protective film no

Standards

European directive RoHs voluntary compliance

Safety

Halogen free yes
 Impact strength IK07

Use conditions

Operating temperature -5...90 °C

temperatur

Ambient temperature -30...90 °C