




ACC816F




## Courbe C, 4500 A / 6 kA type AC

Description	Cond.	Référence
Disj.dif 1P+N 4.5-6kA C-16A 10mA AC	1	ACC816F
Disj.dif 1P+N 4.5kA C-2A 30mA AC	1	ADC802F
Disj.dif 1P+N 4.5kA C-6A 30mA AC	1	ADC806F
Disj.dif 1P+N 4.5kA C-10A 30mA AC	1	ADC810F
Disj.dif 1P+N 4.5kA C-16A 30mA AC	1	ADC816F
Disj.dif 1P+N 4.5kA C-20A 30mA AC	1	ADC820F
Disj.dif 1P+N 4.5kA C-25A 30mA AC	1	ADC825F
Disj.dif 1P+N 4.5kA C-32A 30mA AC	1	ADC832F
Disj.dif 1P+N 4.5kA C-40A 30mA AC	1	ADC840F
Disj.dif 1P+N 4.5kA C-6A 300mA AC	1	AFC806F
Disj.dif 1P+N 4.5kA C-10A 300mA AC	1	AFC810F
Disj.dif 1P+N 4.5kA C-16A 300mA AC	1	AFC816F
Disj.dif 1P+N 4.5kA C-20A 300mA AC	1	AFC820F
Disj.dif 1P+N 4.5kA C-25A 300mA AC	1	AFC825F
Disj.dif 1P+N 4.5kA C-32A 300mA AC	1	AFC832F
Disj.dif 1P+N 4.5kA C-40A 300mA AC	1	AFC840F



ADC816F



## Courbe C, 4500 A / 6 kA type A / HI

Description	Cond.	Référence
Disj.dif 1P+N 4.5kA C-10A 30mA HI	1	ADH810F
Disj.dif 1P+N 4.5kA C-16A 30mA HI	1	ADH816F
Disj.dif 1P+N 4.5kA C-20A 30mA HI	1	ADH820F
Disj.dif 1P+N 4.5kA C-25A 30mA HI	1	ADH825F
Disj.dif 1P+N 4.5kA C-32A 30mA HI	1	ADH832F
Disj.dif 1P+N 4.5kA C-10A 300mA HI	1	AFH810F
Disj.dif 1P+N 4.5kA C-16A 300mA HI	1	AFH816F
Disj.dif 1P+N 4.5kA C-20A 300mA HI	1	AFH820F



ADC916F

## Courbe C, 6000 A / 10 kA type AC

Description	Cond.	Référence
Disj.dif 1P+N 6kA C-6A 30mA AC	1	ADC906F
Disj.dif 1P+N 6kA C-10A 30mA AC	1	ADC910F
Disj.dif 1P+N 6kA C-16A 30mA AC	1	ADC916F
Disj.dif 1P+N 6kA C-20A 30mA AC	1	ADC920F
Disj.dif 1P+N 6kA C-25A 30mA AC	1	ADC925F
Disj.dif 1P+N 6kA C-32A 30mA AC	1	ADC932F
Disj.dif 1P+N 6kA C-40A 30mA AC	1	ADC940F
Disj.dif 1P+N 6kA C-6A 300mA AC	1	AFC906F
Disj.dif 1P+N 6kA C-10A 300mA AC	1	AFC910F
Disj.dif 1P+N 6kA C-16A 300mA AC	1	AFC916F
Disj.dif 1P+N 6kA C-20A 300mA AC	1	AFC920F
Disj.dif 1P+N 6kA C-25A 300mA AC	1	AFC925F
Disj.dif 1P+N 6kA C-32A 300mA AC	1	AFC932F
Disj.dif 1P+N 6kA C-40A 300mA AC	1	AFC940F
Disj. diff. 1P+N 6kA C-16A 10mA AC	1	ACC916F

## Courbe C, 6000 A / 10 kA type A / HI

Description	Cond.	Référence
Disj. diff. 1P+N 6kA C-6A 30mA HI	1	<b>ADH906F</b>
Disj.dif 1P+N 6kA C-10A 30mA HI	1	<b>ADH910F</b>
Disj.dif 1P+N 6kA C-16A 30mA HI	1	<b>ADH916F</b>
Disj.dif 1P+N 6kA C-20A 30mA HI	1	<b>ADH920F</b>
Disj.dif 1P+N 6kA C-25A 30mA HI	1	<b>ADH925F</b>
Disj.dif 1P+N 6kA C-40A 30mA HI	1	<b>ADH940F</b>
Disj.dif 1P+N 6kA C-10A 300mA HI	1	<b>AFH910F</b>
Disj.dif 1P+N 6kA C-16A 300mA HI	1	<b>AFH916F</b>
Disj.dif 1P+N 6kA C-20A 300mA HI	1	<b>AFH920F</b>
Disj.dif 1P+N 6kA C-25A 300mA HI	1	<b>AFH925F</b>
Disj.dif 1P+N 6kA C-32A 300mA HI	1	<b>AFH932F</b>
Disj.dif 1P+N 6kA C-40A 300mA HI	1	<b>AFH940F</b>



ADC816F

## Cache-bornes

Description	Cond.	Référence
Cache bornes plomb jaune Disj.dif 2m	4	<b>AZ010</b>
1 jeu de 2 cache-bornes disj diff. 2M	4	<b>AZ002</b>



AZ010