



NGN116

1 pole, Curve D, 6000 A / 10 kA


Description	Pack qty.	Art No.
MCB 1P 6/10kA D-0.5A 1M	1	NGN100
MCB 1P 6/10kA D-1A 1M	1	NGN101
MCB 1P 6/10kA D-2A 1M	1	NGN102
MCB 1P 6/10kA D-3A 1M	1	NGN103
MCB 1P 6/10kA D-4A 1M	1	NGN104
MCB 1P 6/10kA D-6A 1M	12	NGN106
MCB 1P 6/10kA D-10A 1M	12	NGN110
MCB 1P 6/10kA D-16A 1M	12	NGN116
MCB 1P 6/10kA D-20A 1M	12	NGN120
MCB 1P 6/10kA D-25A 1M	12	NGN125
MCB 1P 6/10kA D-32A 1M	12	NGN132
MCB 1P 6/10kA D-40A 1M	12	NGN140
MCB 1P 6/10kA D-50A 1M	12	NGN150
MCB 1P 6/10kA D-63A 1M	12	NGN163



NGN200

2 pole, Curve D, 6000 A / 10 kA

Description	Pack qty.	Art No.
MCB 2P 6/10kA D-0.5A 2M	1	NGN200
MCB 2P 6/10kA D-1A 2M	1	NGN201
MCB 2P 6/10kA D-2A 2M	1	NGN202
MCB 2P 6/10kA D-3A 2M	1	NGN203
MCB 2P 6/10kA D-4A 2M	1	NGN204
MCB 2P 6/10kA D-6A 2M	1	NGN206
MCB 2P 6/10kA D-10A 2M	1	NGN210
MCB 2P 6/10kA D-16A 2M	1	NGN216
MCB 2P 6/10kA D-20A 2M	1	NGN220
MCB 2P 6/10kA D-25A 2M	1	NGN225
MCB 2P 6/10kA D-32A 2M	1	NGN232
MCB 2P 6/10kA D-40A 2M	1	NGN240
MCB 2P 6/10kA D-50A 2M	1	NGN250
MCB 2P 6/10kA D-63A 2M	1	NGN263



NGN301

3 pole, Curve D, 6000 A / 10 kA

Description	Pack qty.	Art No.
MCB 3P 6/10kA D-0.5A 3M	1	NGN300
MCB 3P 6/10kA D-1A 3M	1	NGN301
MCB 3P 6/10kA D-2A 3M	1	NGN302
MCB 3P 6/10kA D-3A 3M	1	NGN303
MCB 3P 6/10kA D-4A 3M	1	NGN304
MCB 3P 6/10kA D-6A 3M	1	NGN306
MCB 3P 6/10kA D-10A 3M	1	NGN310
MCB 3P 6/10kA D-16A 3M	1	NGN316
MCB 3P 6/10kA D-20A 3M	1	NGN320
MCB 3P 6/10kA D-25A 3M	1	NGN325
MCB 3P 6/10kA D-32A 3M	1	NGN332
MCB 3P 6/10kA D-40A 3M	1	NGN340
MCB 3P 6/10kA D-50A 3M	1	NGN350
MCB 3P 6/10kA D-63A 3M	1	NGN363

4 pole, Curve D, 6000 A / 10 kA

Description	Pack qty.	Art No.
MCB 4P 6/10kA D-0.5A 4M	1	NGN400
MCB 4P 6/10kA D-1A 4M	1	NGN401
MCB 4P 6/10kA D-2A 4M	1	NGN402
MCB 4P 6/10kA D-3A 4M	1	NGN403
MCB 4P 6/10kA D-4A 4M	1	NGN404
MCB 4P 6/10kA D-6A 4M	1	NGN406
MCB 4P 6/10kA D-10A 4M	1	NGN410
MCB 4P 6/10kA D-16A 4M	1	NGN416
MCB 4P 6/10kA D-20A 4M	1	NGN420
MCB 4P 6/10kA D-25A 4M	1	NGN425
MCB 4P 6/10kA D-32A 4M	1	NGN432
MCB 4P 6/10kA D-40A 4M	1	NGN440
MCB 4P 6/10kA D-50A 4M	1	NGN450
MCB 4P 6/10kA D-63A 4M	1	NGN463



NGN401