



LF300G

**gG type**

Description	Pack qty.	Art No.
Cylindrical fuse-links 10x38mm gG 0.5A	10	LF300G
Cylindrical fuse-links 10x38mm gG 1A	10	LF301G
Cylindrical fuse-links 10x38mm gG 2A	10	LF302G
Cylindrical fuse-links 10x38mm gG 4A	10	LF304G
Cylindrical fuse-links 10x38mm gG 6A	10	LF306G
Cylindrical fuse-links 10x38mm gG 8A	10	LF308G
Cylindrical fuse-links 10x38mm gG 10A	10	LF310G
Cylindrical fuse-links 10x38mm gG 12A	10	LF312G
Cylindrical fuse-links 10x38mm gG 16A	10	LF316G
Cylindrical fuse-links 10x38mm gG20A	10	LF320G
Cylindrical fuse-links 10x38mm gG25A	10	LF325G
Cylindrical fuse-links 10x38mm gG 32A	10	LF332G
Industrial fuse-links 14x51 gG 2A	10	LF402G
Industrial fuse-links 14x51 gG 4A	10	LF404G
Industrial fuse-links 14x51 gG 6A	10	LF406G
Industrial fuse-links 14x51 gG 8A	10	LF408G
Industrial fuse-links 14x51 gG 10A	10	LF410G
Industrial fuse-links 14x51 gG 12A	10	LF412G
Industrial fuse-links 14x51 gG 16A	10	LF416G
Industrial fuse-links 14x51 gG 20A	10	LF420G
Industrial fuse-links 14x51 gG 25A	10	LF425G
Industrial fuse-links 14x51 gG 32A	10	LF432G
Industrial fuse-links 14x51 gG 40A	10	LF440G
Industrial fuse-links 14x51 gG 45A	10	LF445G
Industrial fuse-links 14x51 gG 50A	10	LF450G
Cylindrical fuse-links 22x58mm gG 16A	10	LF516G
Cylindrical fuse-links 22x58mm gG 20A	10	LF520G
Cylindrical fuse-links 22x58mm gG 25A	10	LF525G
Cylindrical fuse-links 22x58mm gG 32A	10	LF532G
Cylindrical fuse-links 22x58mm gG 40A	10	LF540G
Cylindrical fuse-links 22x58mm gG 50A	10	LF550G
Cylindrical fuse-links 22x58mm gG 63A	10	LF563G
Cylindrical fuse-links 22x58mm gG 80A	10	LF580G
Cylindrical fuse-links 22x58mm gG 100A	10	LF590G
Cylindrical fuse-links 22x58mm gG 125A	10	LF599G

**aM type**

Description	Pack qty.	Art No.
Cylindrical fuse-links 10x38mm aM 0,5A	10	<b>LF300M</b>
Cylindrical fuse-links 10x38mm aM 1A	10	<b>LF301M</b>
Cylindrical fuse-links 10x38mm aM 2A	10	<b>LF302M</b>
Cylindrical fuse-links 10x38mm aM 4A	10	<b>LF304M</b>
Cylindrical fuse-links 10x38mm aM 6A	10	<b>LF306M</b>
Cylindrical fuse-links 10x38mm aM 8A	10	<b>LF308M</b>
Cylindrical fuse-links 10x38mm aM 10A	10	<b>LF310M</b>
Cylindrical fuse-links 10x38mm aM 12A	10	<b>LF312M</b>
Cylindrical fuse-links 10x38mm aM 16A	10	<b>LF316M</b>
Cylindrical fuse-links 10x38mm aM 20A	10	<b>LF320M</b>
Cylindrical fuse-links 10x38mm aM 25A	10	<b>LF325M</b>
Cylindrical fuse-links 10x38mm aM 32A	10	<b>LF332M</b>
Industrial fuse-links 14x51 aM 2A	10	<b>LF402M</b>
Industrial fuse-links 14x51 aM 4A	10	<b>LF404M</b>
Industrial fuse-links 14x51 aM 6A	10	<b>LF406M</b>
Industrial fuse-links 14x51 aM 8A	10	<b>LF408M</b>
Industrial fuse-links 14x51 aM 10A	10	<b>LF410M</b>
Industrial fuse-links 14x51 aM 12A	10	<b>LF412M</b>
Industrial fuse-links 14x51 aM 16A	10	<b>LF416M</b>
Industrial fuse-links 14x51 aM 20A	10	<b>LF420M</b>
Industrial fuse-links 14x51 aM 25A	10	<b>LF425M</b>
Industrial fuse-links 14x51 aM 32A	10	<b>LF432M</b>
Industrial fuse-links 14x51 aM 40A	10	<b>LF440M</b>
Industrial fuse-links 14x51 aM 45A	10	<b>LF445M</b>
Industrial fuse-links 14x51 aM 50A	10	<b>LF450M</b>
Cylindrical fuse-links 22x58mm aM 16A	10	<b>LF516M</b>
Cylindrical fuse-links 22x58mm aM 20A	10	<b>LF520M</b>
Cylindrical fuse-links 22x58mm aM 25A	10	<b>LF525M</b>
Cylindrical fuse-links 22x58mm aM 32A	10	<b>LF532M</b>
Cylindrical fuse-links 22x58mm aM 40A	10	<b>LF540M</b>
Cylindrical fuse-links 22x58mm aM 50A	10	<b>LF550M</b>
Cylindrical fuse-links 22x58mm aM 63A	10	<b>LF563M</b>
Cylindrical fuse-links 22x58mm aM 80A	10	<b>LF580M</b>
Cylindrical fuse-links 22x58mm aM 100A	10	<b>LF590M</b>
Cylindrical fuse-links 22x58mm aM 125A	10	<b>LF599M</b>



LF300M