



40 x 60, 4 clips

LFS4006009010

Description	Pack qty.	Art No.
Trunking 40060, steel, pure white	12	LFS4006009010
Trunking 40060, steel, galvanized	12	LFS400600VERZ
R 2551 White 9010 Intern.corner lid	4	R25519010
Internal corner lid LFS 40060 galvanized	1	R2551VERZ
R 2552 White 9010 Extern.corner lid	4	R25529010
External corner lid LFS 40060 galvanized	4	R2552VERZ
R 2555 9010	1	R25559010
Flat corner lid LFS 40060 galvanized	8	R2555VERZ
R 2573 White 9010 End cap	5	R25739010
end cap LFS 40060 galvanized	5	R2573VERZ
R 2566 White 9010 T & X piece lid	4	R25669010
cable retainer, LFS, width 60, red	50	M6290
Cable Retainer Steel LFS/FWKP width 60mm	100	R2290VERZ
Coupling LFS height 40 mm	5	R2504VERZ
L 4180 Earth tag	50	L4180VERZ



60 x 60, 4 clips

LFS6006009010

Description	Pack qty.	Art No.
Trunking 60060, steel, pure white	8	LFS6006009010
Trunking 60060, steel, galvanized	8	LFS600600VERZ
ANGLE INTERIEUR PR LFS 60060 LBP	1	R25819010
internal corner lid LFS 60060, galvanize	4	R2581VERZ
ANGLE INTERIEUR PR LFS 60060 LBP	4	R25829010
external corner lid LFS 60060, galvanize	4	R2582VERZ
ANGLE PLAT PR LFS 60060 LBP	6	R25859010
flat corner lid LFS 60060, galvanized	6	R2585VERZ
Embout pour LFS 60060, blanc paloma	10	R26039010
end piece steel LFS E30 60x60mm galvaniz	10	R2603VERZ
R 2606 WHITE 9010 T & X PIECE	4	R26069010
Cable Retainer Steel LFS/FWKP width 60mm	100	R2290VERZ
Coupling LFS height 60 mm	5	R2604VERZ
L 4180 Earth tag	50	L4180VERZ
cable retainer, LFS, width 60, red	50	M6290



60 x 100, 4 clips

LFS6010009010

Description	Pack qty.	Art No.
Trunking 60100, steel, pure white	6	LFS6010009010
Trunking 60100, steel, galvanized	6	LFS601000VERZ
Divider for steel trunking BRS/BRSN/FWKP	32	TWS70VERZ
ANGLE INTERIEUR PR LFS 60100 LBP	4	R26619010
internal corner lid LFS 60100, galvanize	4	R2661VERZ
ANGLE EXTERIEUR PR LFS 60100 LBP	8	R26629010
external corner lid LFS 60100, galvanize	2	R2662VERZ
R 2665 White 9010 Flat corner lid	4	R26659010
flat corner lid LFS 60100, galvanized	4	R2665VERZ
R 2696 White 9010 End cap	6	R26939010
end cap LFS 60100, galvanized	6	R2693VERZ
TE ET CROIX PR LFS 60100 LBP	6	R26469010
Cable Retainer Steel LFS/FWKP width 100	100	R2291VERZ
Coupling LFS height 60 mm	5	R2604VERZ
L 4180 Earth tag	50	L4180VERZ
cable retainer, LFS, width 100, red	50	M6291

60 x 150, 4 clips


Description	Pack qty.	Art No.
Trunking 60150, steel, pure white	6	LFS6015009010
Trunking 60150, steel, galvanized	6	LFS601500VERZ
Divider for steel trunking BRS/BRSN/FWKP	32	TWS70VERZ
R 2701 White 9010 Intgernal corner	5	R27019010
internal corner lid LFS 60150, galvanize	5	R2701VERZ
LFS R2702 EXTERNAL CORN STEEL WHITE 9010	8	R27029010
external corner lid LFS 60150, galvanize	8	R2702VERZ
R 2705 White 9010 Flat corner	4	R27059010
flat corner lid LFS 60150, galvanized	4	R2705VERZ
R 2723 White 9010 End cap	5	R27239010
end cap LFS 60150, galvanized	5	R2723VERZ
T"jet croix pour LFS 60150, blanc palom	6	R26969010
Cable Retainer LFS/FWKP width 150	100	R2292VERZ
Coupling LFS height 60 mm	5	R2604VERZ
L 4180 Earth tag	50	L4180VERZ
cable retainer, LFS, width 150, red	50	M6292



LFS6015009010

60 x 200, 4 clips

Description	Pack qty.	Art No.
Trunking 60200, steel, pure white	4	LFS6020009010
Trunking 60200, steel, galvanized	4	LFS602000VERZ
Divider for steel trunking BRS/BRSN/FWKP	32	TWS70VERZ
ANGLE INTERIEUR PR LFS 60200 LBP	4	R27319010
internal corner lid LFS 60200, galvanize	5	R2731VERZ
ANGLE EXTERIEUR PR LFS 60200 LBP	4	R27329010
external corner lid LFS 60200, galvanize	4	R2732VERZ
R 2735 White 9010 Flat corner lid	4	R27359010
flat corner lid LFS 60200, galvanized	4	R2735VERZ
EMBOUT POUR LFS 60200	6	R27539010
End piece steel zu LFS 60x200mm galvaniz	6	R2753VERZ
TE ET CROIX PR LFS 60200 LBP	6	R27369010
Clamp steel to LFS mit upper top 200mm	100	R2293VERZ
cable retainer, LFS, width 200, red	50	M6293
Coupling LFS height 60 mm	5	R2604VERZ
L 4180 Earth tag	50	L4180VERZ



LFS6020009010