



FL101A

Coffrets métalliques porte pleine

Description	Cond.	Référence
Porte, orion plus, opaque, 250x200x160mm	1	FL101A
Orion+ dis porte op 300x250x160	1	FL102A
Porte, orion plus, opaque, 300x300x160mm	1	FL103A
Orion+ dis porte op 350X300x160	1	FL104A
Orion+ dis porte op 350X300X200	1	FL105A
Porte, orion plus, opaque, 400x300x160mm	1	FL106A
Porte, orion plus, opaque, 400x300x200mm	1	FL107A
Porte, orion plus, opaque, 400x400x200mm	1	FL108A
Porte, orion plus, opaque, 500x300x160mm	1	FL109A
Orion+ dis porte op 500X300X200	1	FL110A
Porte, orion plus, opaque, 500x400x160mm	1	FL111A
Orion+ dis porte op 500X400X200	1	FL112A
Porte, orion plus, opaque, 500x500x200mm	1	FL113A
Orion+ dis porte op 650X400X200	1	FL117A
Porte, orion plus, opaque, 600x400x200mm	1	FL114A
Porte, orion plus, opaque, 600x400x250mm	1	FL115A
Porte, orion plus, opaque, 600x600x250mm	1	FL116A
Orion+ dis porte op 650X400x250	1	FL118A
Orion+ dis porte op 650X500X200	1	FL119A
Orion+ dis porte op 650X500x250	1	FL120A
Porte, orion plus, opaque, 800x500x200mm	1	FL121A
Orion+ dis porte op 800X500x250	1	FL122A
Orion+ dis porte op 800X600x250	1	FL123A
Orion+ dis porte op 800X600X300	1	FL124A
Orion+ dis porte op 950X600x250	1	FL125A
Orion+ dis porte op 950X600X300	1	FL126A
Orion+ dis porte op 950X800x250	1	FL127A
Orion+ dis porte op 950X800X300	1	FL128A
Porte, orion plus, opaque, 1250x600x250mm	1	FL129A
Orion+ dis porte op 1250X800X300	1	FL130A



FL151A

Coffrets métalliques porte transparente

Description	Cond.	Référence
Porte, orion plus, vitrée, 250x200x160mm	1	FL151A
Porte, orion plus, vitrée, 300x250x160mm	1	FL152A
Porte, orion plus, vitrée, 300x300x160mm	1	FL153A
Porte, orion plus, vitrée, 350x300x160mm	1	FL154A
Porte, orion plus, vitrée, 350x300x200mm	1	FL155A
Porte, orion plus, vitrée, 400x300x160mm	1	FL156A
Porte, orion plus, vitrée, 400x300x200mm	1	FL157A
Porte, orion plus, vitrée, 400x400x200mm	1	FL158A
Porte, orion plus, vitrée, 500x300x160mm	1	FL159A
Porte, orion plus, vitrée, 500x300x200mm	1	FL160A
Porte, orion plus, vitrée, 500x400x160mm	1	FL161A
Porte, orion plus, vitrée, 500x400x100mm	1	FL162A
Porte, orion plus, vitrée, 500x500x200mm	1	FL163A
Porte, orion plus, vitrée, 600x400x200mm	1	FL164A
Porte, orion plus, vitrée, 600x400x250mm	1	FL165A
Porte, orion plus, vitrée, 600x600x250mm	1	FL166A
Porte, orion plus, vitrée, 650x400x200mm	1	FL167A
Porte, orion plus, vitrée, 650x400x250mm	1	FL168A
Porte, orion plus, vitrée, 650x500x200mm	1	FL169A
Porte, orion plus, vitrée, 650x500x250mm	1	FL170A
Porte, orion plus, vitrée, 800x500x200mm	1	FL171A
Porte, orion plus, vitrée, 800x500x250mm	1	FL172A
Coffret orion plus vitrée 800x600x250mm	1	FL173A
Porte, orion plus, vitrée, 800x600x300mm	1	FL174A
Porte, orion plus, vitrée, 950x600x250mm	1	FL175A
Porte, orion plus, vitrée, 950x600x300mm	1	FL176A
Porte, orion plus, vitrée, 950x800x250mm	1	FL177A
Porte, orion plus, vitrée, 950x800x300mm	1	FL178A
Porte, orion plus, vitrée, 1250x600x250mm	1	FL179A
Porte, orion plus, vitrée, 1250x800x300mm	1	FL180A

Socles

Description	Cond.	Référence
Socle, orion plus, 150x500x200mm	1	FL957A
Socle coff 150x500x250mm	1	FL958A
Socle coff 150x600x250mm	1	FL959A
Socle coff 150x600x300mm	1	FL960A
Socle coff 150x800x250mm	1	FL961A
Socle coff 150x800x300mm	1	FL962A



FL957A

Serrures


Description	Cond.	Référence
Poignée avec clé N427	10	FL96Z
Jeu serrure 8mm+cle Orion métal	1	FL80Z
Jeu serrure 3mm+clé Orion métal	1	FL95Z
Fermeture, orion plus, 6mm, carrée, 2 pcs.	1	FL82Z
Insert triangle, orion plus, 2pcs.,8mm	1	FL93Z



FL96Z

Pattes de fixation murale

Description	Cond.	Référence
Jeu 4 pattes fix.mur.coff tôle	1	FL85Z



FL85Z

Kits de connexion de masse

Description	Cond.	Référence
Kit connec liaison de terre	1	FL874A



FL874A

Kit d'association verticale

Description	Cond.	Référence
Kit d'association verticale Orion plus	1	FL670A



FL670A