

# Surge protection devices

	<b>Page</b>
SPDs type 1+2	3
SPDs type 1 and type 2 for general protection	4



### SPDs type 1+2 without auxiliary contact

Description	Pack qty.	Art No.
Combined SPD T1+T2 25kA 3P TNC contact	1	<b>SPA800</b>
SPD 4P pluggable 100kA ind. TNS	1	<b>SPN801</b>
SPD 4P pluggable 100kA ind. TT	1	<b>SPN802</b>
Combined SPD T1+T2 4P 25kA TT/TNS cont.	1	<b>SPA801</b>

SPA800



### SPDs type 1+2 with auxiliary contact

Description	Pack qty.	Art No.
Combined SPD T1+T2 25kA 3P TNC contact	1	<b>SPA800</b>
SPD 4P pluggable 100kA ind.+cont. TT	1	<b>SPN802R</b>
Combined SPD T1+T2 4P 25kA TT/TNS cont.	1	<b>SPA801</b>

SPA800



### Accessories for SPN80x

Description	Pack qty.	Art No.
Cartridge 25kA class 1 for SPN8xxx	1	<b>SPN080</b>
Cartridge neutral 25kA class 1 f.SP802x	1	<b>SPN080N</b>
Cartridge N-PE 350V 100kA 1.5kV	1	<b>SPA001N</b>
Cartridge L-N/PEN 350V 25kA	1	<b>SPA081</b>

SPN080

## SPDs type 1

Description	Pack qty.	Art No.
SPD 2P monobloc 12.5kA ind. TT	1	<b>SPA212A</b>
SPD 4P monobloc 12.5kA ind. TT	1	<b>SPA412A</b>



SPA212A

## SPDs type 2 I<sub>max</sub> 65 kA

Description	Pack qty.	Art No.
SPD 2P T2 TNS/TT 65kA Remote contact	1	<b>SPB265R</b>
New SPD 2P pluggable 65kA res.+cont	1	<b>SPN265R</b>
SPD 4P T2 TNS/TT 65kA Remote contact	1	<b>SPB465R</b>
New SPD 4P pluggable 65kA res.+cont	1	<b>SPN465R</b>



SPB265R

## SPDs type 2 I<sub>max</sub> 40 kA

Description	Pack qty.	Art No.
SPD 1P 40kA Typ2 IT	1	<b>SPB113</b>
SPD 1P pluggable 40kA ind.	1	<b>SPN140C</b>
SPD 1P T2 TNC 40kA	1	<b>SPB140D</b>
SPD 2P T2 TNS/TT 40kA	1	<b>SPB240D</b>
SPD 4P T2 TNS/TT 40kA	1	<b>SPB440D</b>
SPD 2P T2 TNS/TT 40kA Remote contact	1	<b>SPB240R</b>
New SPD 2P pluggable 40kA res.+cont	1	<b>SPN240R</b>
SPD 4P T2 TNS/TT 40kA Remote contact	1	<b>SPB440R</b>
New SPD 4P pluggable 40kA res.+cont	1	<b>SPN440R</b>



SPB113

## SPDs type 2 I<sub>max</sub> 15 kA

Description	Pack qty.	Art No.
SPD 2P T2 TNS/TT 15kA	1	<b>SPB215D</b>
SPD 4P T2 TNS/TT 15kA	1	<b>SPB415D</b>
SPD 2P T2 TNS/TT 15kA Remote contact	1	<b>SPB215R</b>
SPD 4P T2 TNS/TT 15kA Remote contact	1	<b>SPB415R</b>
New SPD 4P pluggable 15kA res.+cont	1	<b>SPN415R</b>



SPB215D

## Autoprotected SPD type 2

Description	Pack qty.	Art No.
SPD 2P auto-protected 15kA ind.	1	<b>SPN715D</b>



SPN715D



SPB015D

## Spare cartridges

Description	Pack qty.	Art No.
Cartridge L-N In 5kA I <sub>max</sub> 15kA	1	<b>SPB015D</b>
Cartridge 15kA 275V	1	<b>SPN015D</b>
Cartridge 15kA 275V with reserve	1	<b>SPN015R</b>
Cartridge 40kA T2 IT 440V	1	<b>SPB013</b>
Cartridge 40kA 440V	1	<b>SPN040C</b>
Cartridge L-N In 20kA I <sub>max</sub> 40kA	1	<b>SPB040D</b>
Cartridge 40kA 275V	1	<b>SPN040D</b>
Cartridge 40kA 275V with reserve	1	<b>SPN040R</b>
Cartridge L-N In 20kA I <sub>max</sub> 65kA	1	<b>SPB065R</b>
Cartridge 65kA 275V with reserve	1	<b>SPN065R</b>
Cartridge N-PE In 20kA I <sub>max</sub> 65kA	1	<b>SPB065N</b>
Cartridge neutral 65kA 255V with reserve	1	<b>SPN065N</b>
Cartridge N-PE In 20kA I <sub>max</sub> 40kA	1	<b>SPB040N</b>
Cartridge neutral 40kA 255V	1	<b>SPN040N</b>
Cartridge L-N In 2kA I <sub>max</sub> 8kA	1	<b>SPB008D</b>



SPN408S

## SPDs with low voltage protection level

Description	Pack qty.	Art No.
SPD 4P monobloc 8kA ind.	1	<b>SPN408S</b>
SPD 2P TNS/TT 8kA	1	<b>SPB208D</b>
SPD 4P TNS/TT 8 kA	1	<b>SPB408D</b>