

Degree of protection

Installation type:

Residential, commercial, professional and industrial premises

## IP30

Premises with risk of medium external influences



**mini gamma**  
IP30 without door, plastic,  
surface mounting, 2 to 10 ■



**gamma 13, gamma 18**  
IP30 without door, plastic,  
surface mounting, 13 to 72 ■

## IP40 / IP41

Premises with risk of medium external influences



**consumer unit**  
IP40 with door, metallic,  
surface mounting, 6 to 18 ■



**mini gamma**  
IP40 with door, plastic,  
surface mounting, 2 to 10 ■



**invicta VT consumer unit**  
IP40 with door, metallic, flush  
and surface mounting, 4 to  
20 ■



**gamma 13, gamma 18**  
IP40 with door, plastic,  
surface mounting, 13 to 72 ■



**invicta DR**  
IP40 with door, metallic, flush  
and surface mounting, 16 to  
96 ■



**invicta TP&N 125 and 250**  
IP41 with door, wall mounting  
metallic enclosure, flush and  
surface mounting, 4 to 24  
ways, 13 to 72 ■



**Enclosed fuse combination  
switch**  
IP41 with door, wall mounting  
metallic enclosure, surface  
mounting, 20 to 800 A



**Enclosed load break switch**  
IP40 with door, wall mounting  
metallic enclosure, surface  
mounting, 20 to 1600 A

## IP43 / IP44

Premises with risk of medium external influences



**FW**  
IP44 with door, metallic,  
surface mounting, 36 to 288 ■



**quadro 4**  
IP43 enclosures with door, to  
be assembled, floor standing  
or wall mounting, height 450  
to 1800 mm, width 370 and  
620 mm, up to 630A

## IP54 / IP55

Premises with risk of high external influences



**vega D**  
IP54 with door, plastic, flush  
and surface mounting, 48 to  
168 ■



**vector**  
IP55 with door, plastic,  
surface mounting, 2 to 54 ■



**vector security**  
IP55 with glas door, metallic,  
surface mounting, 6 to 10 ■



**orion.tech IP55 enclosures  
with door**

## IP65

Premises with risk of high external influences



**vector**  
IP65 with door, plastic,  
surface mounting, 3 to 54 ■



**orion plus IP65/66  
enclosures with door**  
- orion polyester,  
- orion steel,  
- orion inox (stainless steel)



**gala**  
IP30 with door, plastic,  
surface mounting, 12 to 48 ■



**volta**  
IP30 with door, plastic, flush  
mounting, 12 to 60 ■



**FW**  
IP30 with door, metallic, flush  
mounting, 36 to 288 ■



**cosmos**  
IP40 with door, plastic, flush  
and surface mounting, 6 to  
24 ■



**vega**  
IP40 with door, plastic,  
surface mounting, 18 to 72 ■



**golf**  
IP40 with door, plastic, flush  
and surface mounting, 8 to  
24 ■



**vega D**  
IP40/41 with door, plastic,  
flush and surface mounting,  
48 to 168 ■



**invicta 250, 400, 630/800  
panel board**  
IP41 with door, wall mounting  
metallic enclosure, surface  
mounting, 2 to 16 ways



**quadro5**  
IP55 with door, floor standing  
or wall mounting metallic and  
monobloc enclosures, height  
510 to 2010 mm width 450 to  
900 mm, up to 630A



**quadro+**  
IP55 floor standing metallic  
enclosures, to be assembled,  
height 1900 and 2100 mm  
width 450 to 1000 mm, up to  
4000A



**quadro automation, FK  
range**  
- metallic automation  
enclosure  
- metallic automation desk