








 260 mm depth		Back plate	Top and bottom panels		Top panel and plinth		Sides (set of 2)	
								
enclosures height with top and plinth	inside height capacity	ref. for enclosure width:		ref. for enclosure width:		ref. for enclosure width:		ref.
370 mm	620 mm	370 mm	620 mm	370 mm	620 mm	370 mm	620 mm	
500 mm	<b>450 mm</b>	FC110	FC210	FC415 FC416	FC425 FC426	FC445 FC446	FC455 FC456	FC010
650 mm	<b>600 mm</b>	FC111	FC211	FC415 FC416	FC425 FC426	FC445 FC446	FC455 FC456	FC011
800 mm	<b>750 mm</b>	FC112	FC212	FC415 FC416	FC425 FC426	FC445 FC446	FC455 FC456	FC012
950 mm	<b>900 mm</b>	FC113	FC213	FC415 FC416	FC425 FC426	FC445 FC446	FC455 FC456	FC013
1100 mm	<b>1050 mm</b>	FC114	FC214	FC415 FC416	FC425 FC426	FC445 FC446	FC455 FC456	FC014
1250 mm	<b>1200 mm</b>	FC115	FC215	FC415 FC416	FC425 FC426	FC445 FC446	FC455 FC456	FC015
1525 mm	<b>1350 mm</b>	FC116	FC216	FC415 FC416	FC425 FC426	FC445 FC446	FC455 FC456	FC016
1675 mm	<b>1500 mm</b>	2xFC112	2xFC112	FC415 FC416	FC425 FC426	FC445 FC446	FC455 FC456	FC012 + FC012
1825 mm	<b>1650 mm</b>	FC118	FC218	FC415 FC416	FC425 FC426	FC445 FC446	FC455 FC456	FC012 + FC013
1975 mm	<b>1800 mm</b>	FC119	FC219	FC415 FC416	FC425 FC426	FC445 FC446	FC455 FC456	2 x FC013

ref. in blue = IP43

		<b>Full door</b>		<b>Transparent door</b>	<b>Assembling kits</b>	
					<b>horizontal</b>	<b>vertical</b>
						
		delivered with keylock		delivered with keylock		
<b>doors height</b>		ref. for enclosure width: 370 mm      620 mm		ref. for enclosure width: 620 mm	ref.	ref.
<b>450 mm</b>		FC310	FC330	FC340	FC120	FC230
<b>600 mm</b>		FC311	FC331	FC341	FC121	FC230
<b>750 mm</b>		FC312	FC332	FC342	FC122	FC230
<b>900 mm</b>		FC313	FC333	FC343	FC123	FC230
<b>1050 mm</b>		FC314	FC334	FC344	FC124	FC230
<b>1200 mm</b>		FC315	FC335	FC345	FC125	FC230
<b>1350 mm</b>		FC316	FC336	FC346	FC126	FC230
<b>1500 mm</b>		FC317	FC337	FC347	FC122 + FC122	FC230
<b>1650 mm</b>		FC318	FC338	FC348	FC122 + FC123	FC230
<b>1800 mm</b>		FC319	FC339	FC349	2 x FC123	FC230